



Specification of Automotive MLCC

• Supplier : Samsung electro-mechanics • Samsung P/N : CL31B104KBP5PNE

• Product : Multi-layer Ceramic Capacitor • Description : CAP, 100nF, 50V, ±10%, X7R, 1206

• AEC-Q 200 Specified

A. Samsung Part Number

<u>CL</u> <u>31</u> <u>B</u> <u>104</u> <u>K</u> <u>B</u> <u>P</u> <u>5</u> <u>P</u> <u>N</u> <u>E</u> ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ①

1	Series	Samsung Multi-layer Ceramic Capacitor					
2	Size	1206 (inch code)	L: 3	.2 ± 0.15	mm	W:	1.6 ± 0.15 mm
3	Dielectric	X7R	(8	nner ele	ctrode		Ni , Open mode
4	Capacitance	100 nF		Terminat	ion		Cu , Ag-epoxy
(5)	Capacitance	±10 %		Plating			Sn 100% (Pb Free)
	tolerance		(9	Product			Automotive
6	Rated Voltage	50 V	1	Grade co	de		Standard
7	Thickness	1.15 ± 0.15 mm	(1) Packagin	g		Embossed Type, 7" reel

B. Reliablility Test and Judgement condition

	Performance	Test condition				
High Temperature	Appearance : No abnormal exterior appearance	Unpowered, 1000hrs@T=150℃				
Exposure	Capacitance Change : Within ±10%	Measurement at 24±2hrs after test conclusion				
	Tan δ : 0.03 max					
	IR : More than 10,000№ or 500№×μF Whichever is Smaller					
Temperature Cycling	Appearance : No abnormal exterior appearance	1000Cycles				
	Capacitance Change : Within ±10%	Measurement at 24±2hrs after test conclusion				
	Tan δ : 0.03 max	1 cycle condition :				
	IR : More than 10,000MΩ or 500MΩ×μF	-55+0/-3℃(15±3min) -> Room Temp(1min.)				
	Whichever is Smaller	-> 125+3/-0 °C (15±3min) -> Room Temp(1min.)				
Destructive Physical No Defects or abnormalities		Per EIA 469				
Analysis						
Moisture Resistance	Appearance : No abnormal exterior appearance	10Cycles, t=24hrs/cycle				
	Capacitance Change : Within ±12.5%	Heat (25~65℃) and humidity (80~98%), Unpowered				
	Tan δ: 0.03 max	measurement at 24±2hrs after test conclusion				
IR : More than 10,000MΩ or 500MΩ×μF						
Humidity Bias	Whichever is Smaller	1000hrs 85°C/85%RH, Rated Voltate and 1.3~1.5V,				
liumuity bias	Capacitance Change: Within ±12.5%	Add 100kohm resistor				
	Tan δ : 0.035 max	Measurement at 24±2hrs after test conclusion				
	IR : More than 500MΩ or 25MΩ×μF	The charge/discharge current is less than 50mA.				
	Whichever is Smaller	The charge, also large saltent is less than some.				
High Temperature Appearance : No abnormal exterior appearance		1000hrs @ TA=125℃, 200% Rated Voltage,				
Operating Life	Capacitance Change : Within ±12.5%	Measurement at 24±2hrs after test conclusion				
	Tan δ : 0.035 max	The charge/discharge current is less than 50mA.				
	IR : More than 1000MΩ or 50MΩ×μF					
	Whichever is Smaller					

	Performance	Test condition				
External Visual	No abnormal exterior appearance	Microscope ('10)				
Physical Dimensions Within the specified dimensions		Using The calipers				
Mechanical Shock	Appearance : No abnormal exterior appearance Capacitance Change : Within ±10% Tan δ, IR : initial spec.	Three shocks in each direction should be applied along 3 mutually perpendicular axes of the test specimen (18 shocks) Peakvalue Duration Wave Velocity 1,500G 0.5ms Half sine 4.7m/sec.				
Vibration	Appearance : No abnormal exterior appearance Capacitance Change : Within ±10% Tan δ, IR : initial spec.	5g's for 20min., 12cycles each of 3 orientations, Use 8"×5" PCB 0.031" Thick 7 secure points on one long side and 2 secure points at corners of opposite sides. Parts mounted within 2" from any secure point. Test from 10~2000Hz.				
Resistance to Solder Heat	Appearance : No abnormal exterior appearance Capacitance Change : Within ±10% Tan δ, IR : initial spec.	Solder pot : 260±5℃, 10±1sec.				
Thermal Shock	Appearance : No abnormal exterior appearance Capacitance Change : Within ±10% Tan δ, IR : initial spec.	-55℃/+125℃. Note: Number of cycles required-300, Maximum transfer time-20 sec, Dwell time-15min. Air-Air				
ESD	Appearance : No abnormal exterior appearance Capacitance Change : Within ±10% Tan δ, IR : initial spec.	AEC-Q200-002				
Solderability	95% of the terminations is to be soldered evenly and continuously	a) Preheat at 155°C for 4 hours, Immerse in solder for 5s at 245±5°C b) Steam aging for 8 hours, Immerse in solder for 5s at 245±5°C c) Steam aging for 8 hours, Immerse in solder for 120s at 260±5°C solder: a solution ethanol and rosin				
Electrical Characterization	Capacitance : Within specified tolerance Tan δ (DF) : 0.025 max. IR(25 °C) : More than 10,000μΩ or 500μΩ×μF IR(125 °C) : More than1,000μΩ or 10μΩ×μF Whichever is Smaller Dielectric Strength	The Capacitance /D.F. should be measured at 25℃, 1½±10%, 1.0±0.2Vrms I.R. should be measured with a DC voltage not exceeding Rated Voltage @25℃, @125℃ for 60~120 sec. Dielectric Strength: 250% of the rated voltage for 1~5 seconds				
Board Flex	Appearance : No abnormal exterior appearance Capacitance Change : Within ±10%	, , , , , , , , , , , , , , , , , , ,				
Terminal Strength(SMD)	Appearance : No abnormal exterior appearance Capacitance Change : Within ±10%	18N, for 60±1 sec.				
Beam Load	Destruction value should not be exceed Chip Length ≥ 3.2mm a) Chip Thickness < 1.25mm : 15N b) Chip Thickness ≥ 1.25mm : 54.5N	Beam speed 2.5±0.25mm/sec				
Temperature Characterisitcs	X7R (From -55℃ to 125℃, Capacitance change shot	ud be within ±15%)				

C. Recommended Soldering method :

^{*} For the more detail Specification, Please refer to the Samsung MLCC catalogue.