


Vishay General Semiconductor

Surface Mount Schottky Barrier Rectifiers



PRIMARY CHARACTERISTICS				
I _{F(AV)}	1.0 A			
V_{RRM}	30 V, 40 V			
I _{FSM}	25 A			
V _F at I _F = 1.0 A	0.41 V			
T _J max.	150 °C			

TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, dc-to-dc converters, and polarity protection applications.

FEATURES

• Very low profile - typical height of 0.68 mm



• Ideal for automated placement



Low forward voltage drop, low power losses

ROHS COMPLIANT HALOGEN

FREE

High efficiency

 Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C

 Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC

· Halogen-free

MECHANICAL DATA

Case: MicroSMP

Molding compound meets UL 94V-0 flammability

rating.

Base P/N-E3 - RoHS compliant, commercial grade
Base P/N-M3 - halogen-free and RoHS compliant,

commercial grade

Terminals: Matte tin plated leads, solderable per

J-STD-002 and JESD22-B102

E3 and M3 suffix meets JESD 201 class 1A whisker

test

Polarity: Color band denotes the cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)						
PARAMETER	SYMBOL	MSS1P3	MSS1P4	UNIT		
Device marking code		13	14			
Maximum repetitive peak reverse voltage	V _{RRM}	RM 30 40		V		
Maximum average forward rectified current (Fig. 1)	I _{F(AV)}	1.0		Α		
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	25		А		
Operating junction and storage temperature range	T _J , T _{STG}	- 55 to + 150		°C		

MSS1P3 & MSS1P4

Vishay General Semiconductor



ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)						
PARAMETER	TEST C	ONDITIONS	SYMBOL	TYP.	MAX.	UNIT
Maximum instantaneous forward voltage ⁽¹⁾	I _F = 0.5 A I _F = 1.0 A	T _J = 25 °C	V_{F}	0.41 0.48	- 0.55	· V
	I _F = 0.5 A I _F = 1.0 A	T _J = 125 °C		0.32 0.41	- 0.46	
Maximum reverse current (2)	rated V _R	T _J = 25 °C T _J = 125 °C	I _R	8.5 4.5	200 15	μA mA
Typical junction capacitance	4.0 V, 1 MHz		CJ	50	-	pF

Notes:

(1) Pulse test: 300 µs pulse width, 1 % duty cycle

(2) Pulse test: Pulse width ≤ 40 ms

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	MSS1P3	MSS1P4	UNIT	
Typical thermal resistance ⁽¹⁾	$egin{array}{c} R_{ hetaJA} \ R_{ hetaJL} \ R_{ hetaJC} \end{array}$	125 30 40		°C/W	

Note:

(1) Thermal resistance from junction to ambient and junction to lead mounted on P.C.B. with 6.0 x 6.0 mm copper pad areas $R_{\theta JL}$ is measured at the terminal of cathode band. $R_{\theta JC}$ is measured at the top center of the body

ORDERING INFORMATION (Example)						
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
MSS1P4-E3/89A	0.006	89A	4500	7" diameter plastic tape and reel		
MSS1P4-M3/89A	0.006	89A	4500	7" diameter plastic tape and reel		

RATINGS AND CHARACTERISTICS CURVES

(T_A = 25 °C unless otherwise noted)




Figure 1. Maximum Forward Current Derating Curve




Figure 2. Forward Power Loss Characteristics



Vishay General Semiconductor




Figure 3. Typical Instantaneous Forward Characteristics




Figure 5. Typical Junction Capacitance




Figure 4. Typical Reverse Characteristics




Figure 6. Typical Transient Thermal Impedance

(0.50)

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

MicroSMP 0.059 (1.50) 0.030 (0.75) Cathode Band 0.043 (1.10) 0.022 (0.55) 0.055 (1.40) 0.047 (1.20) 0.030 (0.75) 0.039 (0.98) 0.031 (0.78) 0.022 (0.55) 0.091 (2.30) 0.083 (2.10) 0.106 (2.70) 0.091 (2.30) **Mounting Pad Layout** 0.079 0.032 (2.00)(0.80) 0.029 (0.73) 0.032 0.043 0.025 (0.63) (1.10) (0.80) ŧ. 0.011 (0.27) 0.005 (0.12) 0.020



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Revision: 18-Jul-08

Document Number: 91000 www.vishay.com