






RoHS Compliant

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
A0	—	01/09'22	The first release	PansLee
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				



Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	AP-DPDT INDUSTRIAL RELAY						
PART NO.	AP2CXXX00G				DWG NO.	8AP2C-0001	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		PansLee 2022.1.09	PansLee 2022.1.09			UNIT: mm	X ±0.50
						SCALE: NONE	X.X ±0.10
						SHEET: 01/02	X° ±1°
						REV.: A0	

1		2		3		4		5		6		7	
RoHS Compliant								Rev. SIGN DATE		DESCRIPTION		APPROVER	
								A0 — 01/09'22		The first release		PansLee	
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!													
线圈参数,在23 ℃环境下 Coil parameters (At 23 ℃)													
线圈规格代码 Coil voltage code		线圈额定电压(V)Reted coil voltage		线圈电阻(Ω)Coil resistance ± 10%		线圈功率 Power Consumption		动作电压 Operate voltage		释放电压 Release voltage		线圈最大电压 Max. allowable voltage	
D5		5VDC		47		0.53W		70% Maximum		15% Minimum		170% Maximum	
D6		6VDC		68									
D12		12VDC		275									
D24		24VDC		1100									
D36		36VDC		24400									
D48		48VDC		4300									
D110		110VDC		22860									
注Annotation: 交流线圈电源频率50~60Hz. The frequency of AC Coil is 50 ~ 60 Hz.													
触点参数													
●触点形式Contact Form: DPDT													
●接触电阻Contact Resistance: 50mA,在6VDC@100mA													
●触点材质Contact Material: AgNi													
●阻性负载Resistive load: 5A@30VDC/250VAC ,50~60Hz													
●感性负载: 3A,30VDC,L/R=7ms													
2A,250VAC,cosΦ=0.4													
●电气寿命Electrical Life: 10万次 100,000 operations at Rated Resistive Load.													
●机械寿命Mechanical Life: 3000万次 10,000,000 operations at No Load condition.													
综合性能参数													
●绝缘电阻Insulation resistance:1000M Ω @500VDC													
●介质耐压(初始) Dielectric strength (initial) :同极触点间1000VAC,1Min;													
异极触点间3000VAC,1Min;													
线圈触点间5000VAC,1Min													
Between open contact 1000VAC,1Min;													
Between different pole 3000VAC,1Min;													
Between contact and coil 5000VAC,1Min													
●动作时间Operate time: 15ms Max.													
●释放时间Release time: 15ms Max.													
使用环境Service environment													
●使用环境温度Ambient temperature: -45~+70度													
●湿度Ambient humidity: 5%-85%													
●抗冲击Shock resistance: 98m/s², 储存980m/s²													
●耐振动Vibration resistance: 10-55Hz, 双振幅1.5mm													
其它Other													
●基座材质The base material:PBT,黑色 black													
●防尘外壳Dust-proof cover: 透明PC Transparent PC													
●重量Weight: About 17g													
●重點尺寸Critical dimension: ▲													
继电器规格号示例Part Number Description:													
AP 2C XXXX 00G													
标准品, 符合环保RoHS: RoHS compliant (lead<4%) In copper Alloy													
线圈规格代码Coil Voltage: D024:DC24V 、.....													
触点形式Contact Form: 2C: DPDT, 两组转换Two groups switch													
产品型别Series Designation : AP Series													
Amphenol ANYTEK										CUSTOMER COPY			
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD													
TITLE		AP-DPDT INDUSTRIAL RELAY											
PART NO.		AP2CXXXX00G						DWG NO.		8AP2C-0001			
APPROVED		CHECKED		DESIGNED		DRAWN		CUST NO.		Tolerance			
				PansLee 2022.1.09		PansLee 2022.1.09				UNIT: mm		X ±0.50	
										SCALE: NONE		X.X ±0.10	
								SHEET: 02/02		REV.: A0		X° ±1°	