

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 6-position, free cable end, on Socket straight 1/2"-20UNF, coding: C, cable length: Free input (0.2 ... 40.0 m)

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Adapted: 1/2"-20UNF connectors with C-coding for the North American market

Commercial data

Item number	1547290
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF17
Product key	AF1EEA
Catalog page	Page 100 (PC-2007)
Customs tariff number	85444290
Country of origin	PL

SAC-6P-MICFS/.../... - Sensor/actuator cable



1547290

<https://www.phoenixcontact.com/us/products/1547290>

Technical data

Notes

Trade restriction

CE note	The products are offered exclusively for export outside the EU and the European Economic Area.
---------	--

Product properties

Product type	Sensor/actuator cable
Application	Standard
Number of positions	6
No. of cable outlets	1
Shielded	no
Coding	C

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Brass, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V AC
	30 V DC
Nominal current I_N	2 A
Test voltage	800 V

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	No

Connector

SAC-6P-MICFS/.../... - Sensor/actuator cable



1547290

<https://www.phoenixcontact.com/us/products/1547290>

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket straight 1/2"-20UNF
Number of positions	6
Coding type	C

Cable/line

Cable length	Free input (0.2 ... 40.0 m)
--------------	-----------------------------

PVC yellow 105 °C [542]

Cable weight	63 kg/km
Number of positions	6
Shielded	no
Cable type	PVC yellow 105 °C [542] PVC yellow 105 °C 542
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross section	0.34 mm²
Wire diameter incl. insulation	1.55 mm ±0.05 mm
External cable diameter	6.4 mm
Outer sheath, material	PVC
External sheath, color	yellow
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	red/black, red/white, red, green, red/yellow, red/blue
Thickness, insulation	≥ 0.38 mm (Core insulation) ≥ 0.76 mm (Outer cable sheath)
Overall twist	Six pairs around the filler to the core
Max. conductor resistance	≤ 58 Ω/km
Insulation resistance	≥ 100 MΩ*km
Nominal voltage, cable	300 V
Test voltage	3000 V
Ambient temperature (operation)	-25 °C ... 105 °C (cable, fixed installation) -5 °C ... 105 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 IP67 IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)

SAC-6P-MICFS/.../... - Sensor/actuator cable

1547290

<https://www.phoenixcontact.com/us/products/1547290>




Drawings

Circuit diagram



Contact assignment of 1/2" UNF plugs / sockets

Dimensional drawing



1/2"-20UNF socket, straight


SAC-6P-MICFS/.../... - Sensor/actuator cable

1547290

<https://www.phoenixcontact.com/us/products/1547290>



Schematic diagram



Pin assignment 1/2"-20UNF socket, 6-pos., view female side

SAC-6P-MICFS/.../... - Sensor/actuator cable



1547290

<https://www.phoenixcontact.com/us/products/1547290>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1547290>



UL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	4 A	-	-



cUL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	4 A	-	-



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

cULus Listed

SAC-6P-MICFS/.../... - Sensor/actuator cable



1547290

<https://www.phoenixcontact.com/us/products/1547290>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-6P-MICFS/.../... - Sensor/actuator cable



1547290
<https://www.phoenixcontact.com/us/products/1547290>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com