







N = Number of poles

Dim.L=Nx3.5+0.35

Dim.P=(N-1)x3.5

Dim.B=(N-1)x3.5+5.5

Poles	Dim.	Dim.L	Dim.P	Dim.B
2-6p		±0.25	±0.20	±0.20
7-12p		±0.30	±0.25	±0.25
13-16p		±0.35	±0.30	±0.30



SIGN	DATE	DESCRIPTION	APPROVER
△	04/05`12	Operating temperature is changed from -45°C to +130°C to -45°C to +65°C	Guoxue
△	04/05`12	The PART NO is changed	Guoxue
△	04/05`12	The Material is changed	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Materials

- △ Item① Terminal body:High temp. polyamide (UL94V-0)
- Item② Terminal screw: Steel Zinc plating "+/-" slot type
- Item③ Wire guard :Stainless steel
- Item④ Terminal :Brass(CuZn) Tin Plated
- Item⑤ Terminal Cover: High temp. polyamide (UL94V-0)

Electrical UL

- Voltage rating: 150VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 16-26
- Stranded wire(AWG): 16-26
- Torque(Lb-In): 2.0
- Screw: M2.0
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -45°C to +65°C
- Soldering temperature: 280°C/10 Sec
- Safety Approval:
- Critical dimension:▽
- Part No:

△ EC xx 10 x 1 Bxxx G

Solid block
02 2 POLES
03 3 POLES
...
16 16 POLES

COLOR
0 Black (RAL9005)

B000 "①" Logo
B00A "ANY" Logo
...
Any special item by customer request, please contact sales department

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	EC 3.5 Series "+/-"Screw With pillar (With cover & tape reel)				DWG NO.	8EC0007	
PART NO.	ECxx10x1BxxxG				CUST NO.		
APPROVED	CHECKED	DESIGNED	DRAWN			Tolerance	
		Guoxue 2012.07.28	Guoxue 2012.07.28			UNIT: mm	X. ±0.5
						SCALE: NONE	X.X ±0.3
							X.XX ±0.1
							X° ±1°