

E

D

C

B

A

| SIGN                                           | DATE       | DESCRIPTION                      | APPROVER |
|------------------------------------------------|------------|----------------------------------|----------|
| △                                              | 2010.01.29 | Add cULus standard               | Jacke    |
| △                                              | 2010.01.29 | The wire strip length is changed | Jacke    |
| △                                              | 2010.03.31 | Add the 2p mark                  | Jacke    |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |            |                                  |          |

Material:

- Item ㉑ Terminal(housing): Thermoplastic (UL94V-0)
- Item ㉒ Clamp: Brass(CuZn) Ni plated
- Item ㉓ Female contact: PhBz Tin plated
- Item ㉔ Terminal Screw: Steel zinc plated.

Electrical: cULus

- Voltage rating: 300 V
- Current rating: 15 A
- Wire range:
- Solid wire(AWG):12-22
- Stranded wire(AWG):12-22
- Torque: 4.3 Lb-In
- Screw:M3
- △ ● Wire strip length:7-8 mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C
- △ ● Safety Approval: 

E Z xx 5 1 x 0 xxxx G

No. OF POLES  
02: 2 POLES  
:  
24: 24 POLES

COLOR

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)


G: Pb&lt;4000ppm

0000: "@" Logo (Standard)  
000A: "ANYTEK" Mark

Any special item by  
customer request.  
please contact sales  
department.




△



|      |       |       |       |       |       |       |       |        |        |        |        |        |
|------|-------|-------|-------|-------|-------|-------|-------|--------|--------|--------|--------|--------|
| POLE |       | 2     | 3     | 4     | 5     | 6     | 7     | 8      | 9      | 10     | 11     | 12     |
| A    |       | 10.46 | 15.54 | 20.62 | 25.70 | 30.78 | 35.86 | 40.94  | 46.02  | 51.10  | 56.18  | 61.26  |
| B    |       | 5.08  | 10.16 | 15.24 | 20.32 | 25.40 | 30.48 | 35.56  | 40.64  | 45.72  | 50.80  | 55.88  |
| Tol. | ±0.15 |       |       |       |       |       | ±0.20 |        |        |        |        |        |
| POLE | 13    | 14    | 15    | 16    | 17    | 18    | 19    | 20     | 21     | 22     | 23     | 24     |
| A    | 66.34 | 71.42 | 76.50 | 81.58 | 86.66 | 91.74 | 96.82 | 101.90 | 106.98 | 112.06 | 117.14 | 122.22 |
| B    | 60.96 | 66.04 | 71.12 | 76.20 | 81.28 | 86.36 | 91.44 | 96.52  | 101.60 | 106.68 | 111.76 | 116.84 |
| Tol. | ±0.25 |       |       |       |       |       | ±0.30 |        |        |        |        |        |

**ANYTEK****CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |                |                     |                     |                                                                                       |              |  |         |            |  |  |  |  |
|----------|----------------|---------------------|---------------------|---------------------------------------------------------------------------------------|--------------|--|---------|------------|--|--|--|--|
| TITLE    | EZ-5.08 Series |                     |                     |                                                                                       |              |  |         |            |  |  |  |  |
| PART NO. | EZxx51x0xxxxG  |                     |                     |                                                                                       |              |  | DWG NO. | 8EZ0101    |  |  |  |  |
| APPROVED | CHECKED        | DESIGNED            | DRAWN               | CUST NO.                                                                              |              |  |         | Tolerance  |  |  |  |  |
|          |                | Jacke<br>2010.03.31 | Jacke<br>2010.01.29 |  | UNIT: mm     |  |         | X. ±0.50   |  |  |  |  |
|          |                |                     |                     |                                                                                       | SCALE: NONE  |  |         | X.X ±0.30  |  |  |  |  |
|          |                |                     |                     |                                                                                       | SHEET: 01/01 |  |         | X.XX ±0.10 |  |  |  |  |
|          |                |                     |                     |                                                                                       | REV.: D      |  |         | X° ±1°     |  |  |  |  |