

SIGN	DATE	DESCRIPTION	APPROVER
△	7/23'08	With flange type is changed	Marvin
△	7/23'08	Operating temperature is changed	Marvin
△	2009.11.14	The design is changed from the round hole to hexagonal hole.	Jacke
△	2010.01.12	Add cULus standard	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Materials

Item a Terminal body:Thermoplastic (UL94V-0)
Item b Female contact:PhBz(CuSn), Tin plated
Item c With Flange Nut :Brass M2.5

Electrical





- Voltage rating: 300V AC
- Current rating: 8A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- △ ● Safety Approval: 

V7 xx 1 2 x 1 xxxx G

No. OF POLES
02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL 7035/D)

G: Pb<40000ppm
0000: "@ " Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer request, please contact sales department.




P.C.B. LAYOUT

Poles	02	03	04	05	06	07	08	09	10	11	12	13
Dim A	6.3	9.8	13.3	16.8	20.3	23.8	27.3	30.8	34.3	37.8	41.3	44.8
Dim B	3.5	7.0	10.5	14.0	17.5	21.0	24.5	28.0	31.5	35.0	38.5	42.0
Dim C	17.7	21.2	24.7	28.2	31.7	35.2	38.7	42.2	45.7	49.2	52.7	56.2
TOL	±0.1				±0.15				±0.2			
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim A	48.3	51.8	55.3	58.8	62.3	65.8	69.3	72.8	76.3	79.8	83.3	
Dim B	45.5	49.0	52.5	56.0	59.5	63.0	66.5	70.0	73.5	77.0	80.5	
Dim C	59.7	63.2	66.7	70.2	73.7	77.2	80.7	84.2	87.7	91.2	94.7	
TOL	±0.2		±0.25				±0.30					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	V7 3.5 series Right angle With flange										
PART NO.	V7xx12x1xxxxG				DWG NO.	8V70003					
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.					Tolerance		
		Jacke 2010.01.14	Jacke 2010.01.14						UNIT: mm		X. ±0.5
					SCALE: NONE		X.X ±0.3				
					SHEET: 01/01		X.XX ±0.1				
					REV.: E		X° ±1°				