






RECOMMENDED PCB LAYOUT



SECTION P-P

SIGN	DATE	DESCRIPTION	APPROVER
△	2009.09.28	The design is changed from the round hole to hexagonal hole	Jacke
△	2009.09.28	The current rating is changed from 15A to 10A	Jacke
△	2009.09.28	Add UL standard	Jacke
△	2012.04.16	Flange nut is changed	Chen Bo
△	2012.04.16	The dimension C & D & 1.0 are added	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ① Male contact pin: Copper, Tin plated
- Item ② With flange nut: brass M2.5
- Item ③ Terminal(housing): Thermoplastic (UL94 V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:
- Critical dimension: ▽

VF xx 52 x 1 xxxx G		RoHS compliant (lead<4%) In copper Alloy
Poles		0000 Standard @ Logo
04 2x2Poles		000A Standard ANY Logo
06 2x3Poles		Any special item by customer request, please contact sales department.
...		
48 2x24Poles		
Color		
0 Black (RAL9005)		
2 Red (RAL3001/D)		
3 Orange(RAL2011/P)		
4 Yellow(RAL1018/A)		
5 Green(RAL6018/T)		
6 Blue (RAL5015/A)		
8 Grey(RAL7035/D)		

N=NUMBER OF CONTACTS

Dimension	TOL				
	2x2P-2x5P	2x6P-2x10P	2x11P-2x15P	2x16P-2x20P	2x21P-2x24P
Dim L (N/2+2)×5.08	±0.15	±0.20	±0.25	±0.30	±0.35
Dim B (N/2-1)×5.08	±0.15	±0.20	±0.25	±0.30	±0.35
Dim C (N/2-1)×5.08	±0.15	±0.20	±0.25	±0.30	±0.35
Dim D (N/2-1)×5.08+10.16	±0.15	±0.20	±0.25	±0.30	±0.35

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VF-5.08 Series Right angle W/Flange				
PART NO.		VFxx52x1xxxxG		DWG NO.	8VF0101	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Chen Bo 04/16 12	Chen Bo 04/16 12		UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
					SHEET: 01/01	X° ±1°
					REV.: D	