

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 2-position, Plug straight 1/2"-20UNF, coding: C, on Socket angled 1/2"-20UNF, coding: C, cable length: Free input (0.2 ... 40.0 m)

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Adapted: 1/2"-20UNF connectors with C-coding for the North American market

Commercial data

Item number	1547326
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF17
Product key	AF1EAA
Catalog page	Page 96 (PC-2007)
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85444290
Country of origin	US

Technical data

Notes

Trade restriction

CE note	The products are offered exclusively for export outside the EU and the European Economic Area.
---------	--

Product properties

Product type	Sensor/actuator cable
Application	Standard
Number of positions	2
No. of cable outlets	1
Shielded	no
Coding	C

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Brass, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	250 V AC
	250 V DC
Nominal current I_N	4 A
Test voltage	2500 V

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	No

Connector

SAC-2P-MICMS-MICFR/.../... - Sensor/actuator cable



1547326

<https://www.phoenixcontact.com/us/products/1547326>

Connection 1

Type	Plug straight 1/2"-20UNF
Number of positions	2
Coding type	C

Connection 2

Type	Socket angled 1/2"-20UNF
Number of positions	2
Coding type	C

Cable/line

Cable length	Free input (0.2 ... 40.0 m)
--------------	-----------------------------

PVC yellow 105 °C [542]

Cable weight	32 kg/km
UL AWM Style	2517 (105 °C / 300 V)
Number of positions	2
Shielded	no
Cable type	PVC yellow 105 °C [542] PVC yellow 105 °C 542
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross section	2x 0.34 mm ²
Wire diameter incl. insulation	1.55 mm ±0.05 mm
External cable diameter	4.90 mm ±0.15 mm
Outer sheath, material	PVC
External sheath, color	yellow
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue
Thickness, insulation	≥ 0.38 mm (Core insulation)
Thickness, outer sheath	≥ 0.76 mm
Overall twist	2 wires, twisted
Max. conductor resistance	58 Ω/m (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Flame resistance	According to DIN EN 60332-1-2
Ambient temperature (operation)	-25 °C ... 105 °C (Cable) -5 °C ... 105 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

IP65

SAC-2P-MICMS-MICFR/.../... - Sensor/actuator cable



1547326

<https://www.phoenixcontact.com/us/products/1547326>

Degree of protection	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)

SAC-2P-MICMS-MICFR/.../... - Sensor/actuator cable


1547326

<https://www.phoenixcontact.com/us/products/1547326>




Drawings

Circuit diagram



Contact assignment of 1/2" UNF plugs / sockets

Dimensional drawing




1/2"-20UNF socket, angled

1547326


<https://www.phoenixcontact.com/us/products/1547326>

Schematic diagram



Pin assignment 1/2"-20UNF socket, 2-pos., view female side

Schematic diagram




Pin assignment 1/2"-20UNF plug, 2-pos., view male side

1547326

<https://www.phoenixcontact.com/us/products/1547326>

Dimensional drawing



1/2"-20UNF plug, straight

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1547326>

	UL Listed Approval ID: FILE E 221474			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	300 V	4 A	-	-

	cUL Listed Approval ID: FILE E 221474			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	300 V	4 A	-	-

	EAC-RoHS Approval ID: RU D-DE.HB35.B.00387			

cULus Listed

SAC-2P-MICMS-MICFR/.../... - Sensor/actuator cable



1547326

<https://www.phoenixcontact.com/us/products/1547326>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%