







P.C.B LAYOUT(Top View)



DIM		TOL			
		2P-4P	5P-10P	11P-16P	17P-18P
Dim A	(N+2)×7.62	±0.20	±0.30	±0.40	±0.50
Dim B	(N-1)×7.62	±0.20	±0.30	±0.40	±0.50

SIGN	DATE	DESCRIPTION	APPROVER
△	2009.1.7	APPROVAL: cULus	kind
△	11/20'12	Change the screw plating specification	Jacky
△	11/20'12	Change the electrical specification	Jacky
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL

RATED VOLTAGE & CURRENT:

300 V, 15 A

WITHSTAND VOLTAGE:

AC 2000 V/Min

INSULATION RESISTANCE:

1000 MΩ OR MORE AT DC 500 V

△ OPERATING TEMPERATURE RANGE:

-40 °C ~ +115 °C

SCREW TORQUE VALUE:

5.2 Lb-In.

WIRE RANGE:

14 ~ 22 AWG

1) MOLDED PARTS:

THERMOPLASTIC, UL 94 V-0 BLACK

2) TERMINAL:

BRASS, 0.8t, Tin PLATED

△ 3) TERMINAL SCREWS:

STEEL, M3

△ APPROVAL: cULus

PART No.:

Critical dimension: ▽

YK 306xx 3 x x 00G

NO. OF POLES

02: 2 POLES

03: 3 POLES

04: 4 POLES

...

18: 18 POLES

G:RoHS compliant(lead<4%)
in copper alloy

MARK

0: "0" MAK

1: "ANY" MAK

TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F

△ 1: TERMINAL: G/F, SCREW: Zinc

2: TERMINAL: Sn, SCREW: G/F

△ 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-306With Flange & W/o cover Series				
PART NO.	YK306xx3xx00G			DWG NO.	8YK0004-306	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
		Jacky 2012.11.20	Jacky 2012.11.20			
				SHEET: 01/01	SCALE: NONE	X.X ±0.30
					REV.: C	X° ±1°
						X.XX ±0.10
						X. ±0.50