






UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN MM



STRIP DIMENSIONS



SCALE 3:1

ELECTRICAL CHARACTERISTICS:

NOMINAL IMPEDANCE: 50Ω
FREQUENCY RANGE: DC TO 1 GHz
VSWR: 1.3:1 MAX.
INSERTION LOSS: 0.2 dB AT 3 GHz
OPERATING VOLTAGE (RMS): 500 V MAX. AT SEA LEVEL
DWV: 1500 V MAX. AT SEA LEVEL
CONTACT RESISTANCE: 1.5 mΩ MAX.
INSULATION RESISTANCE: 5000 MΩ MIN.

MECHANICAL CHARACTERISTICS:

MATING CYCLES: 500 CYCLES MIN.
INTERFACE DIMENSIONS: CONFORMS TO MIL-C-39012

ENVIRONMENTAL CHARACTERISTICS:

TEMPERATURE RANGE: -65 °C TO +165 °C

	PART	MATERIAL	FINISH
1	BODY	BRASS	NICKEL
2	DIELECTRIC	DELRIN	WHITE
3	CONTACT	BRASS	GOLD
4	GASKET	RUBBER	RED
5	FERRULE	BRASS	NICKEL
6	NUT	BRASS	NICKEL
7	WASHER	STEEL	NICKEL

CRIMP DETAILS	
FERRULE	CONTACT
6.50 (0.256")	1.73 (0.068")
	OR SOLDER

DRAWN BY:
M.BARRACLOUGH



CINCH CONNECTORS LTD
SHIREOAKS ROAD, WORKSOP
S80 3HA (01909) 474131

CAGE CODE:
U1718

DRAWING TITLE:
BNC BULKHEAD CRIMP JACK FOR RG59

DRAWING NUMBER:
VB40-2031

SCALE:
NTS

SHEET:
1 OF 1

A3

DRAWN TO BS 8888
TOLERANCES (unless specified): ISO 2768mK



THIS DRAWING IS COPYRIGHT AND IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY WITHOUT PRIOR WRITTEN CONSENT OF CINCH LTD.
ATTENTION IS DRAWN TO THE FACT THE ARTICLE DISCLOSED MAY BE COVERED BY BRITISH OR FOREIGN PATENTS, GRANTED OR PENDING OR REGISTERED DESIGN.

mm 10 50 100