

SIGN	DATE	DESCRIPTION	APPROVER
△	07/13`12	The dimension is added	Chen Bo
△	03/04`14	update the drawing	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			





Material:

- Item a Terminal(housing): Thermoplastic,UL 94 - V0.
- Item b Male contact pin: Copper, Gold plated
- Item c With flange nut : Steel zinc plated M3

Electrical: cULus / IEC

- Voltage rating: 300V / 1000V
- Current rating: 55A / 76A
- Withstanding Voltage: 1.6 KV / 8 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus
- Critical dimension: ▽

EW xx 62 x 2 xxxx G		
Solid Block 02 2Contacts 03 3Contacts 12 12Contacts	Color	→ G RoHS compliant (lead<4%) In copper Alloy
		→ 0000 Standard @ Logo
		→ 000A Standard ANY Logo
		Any special item by customer request, please contact sales department.
	0	Black (RAL9005)
	2	Red (RAL3001/D)
	3	Orange(RAL2011/P)
	4	Yellow(RAL1018/A)
	5	Green(RAL6018/T)
	6	Blue (RAL5015/A)
	8	Grey(RAL7035/D)
	9	White(RAL1102)
	C	Green(RAL6018/U)



SECTION A-A

Dimension

Dim L	(N+1)×10.16+7.6
Dim B	(N-1)×10.16
Dim C	(N+1)×10.16
Dim D	(N-1)×10.16

N=Number of poles

POLES	TOL
2p-5p	±0.25
6p-8p	±0.35
9p-12p	±0.45

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	EW 10.16 Series 2p-12p Right -Angle W/F angle (up)						
PART NO.	EWxx62x2xxxxG			DWG NO.	8EW0005		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Chen Bo	Chen Bo			UNIT: mm	X. ±0.50
		03/04`14	03/04`14			SCALE: NONE	X.X ±0.30
						REV.: D	X.XX ±0.10
							X° ±1°

SHEET: 01/01

REV.: D