








PANEL CUT-OUT



SPECIFICATION: (SWITCH)

1. Electrical rating : 6A 250VAC & 12A 125VAC [UL]
4(1)A 250VAC [VDE . ENEC10]
2. Contact resistance : <20mΩ (Initial)
3. Insulation resistance : 100MΩ (500VDC between open contacts)
4. Dielectric strength : 1500V 1 minute

SPECIFICATION:

1. Insulation Resistance: Over 100MΩ at 500V DC.
2. Dielectric strength: 2000V AC 1 Minute.
3. Body Material: Thermoplastic 94V-2~V-0.

Rating:AC 15A 250V


Mark	Safety Regulation
	CULUS

Rating:AC 10A 250V

Mark	Safety Regulation
	VDE
	ENEC
	CCC



富灣股份有限公司
RICH BAY COMPANY LTD.
台北縣樹林市東興街57號
NO. 57, Tung Hsing St., Shu-Lin Town,
Taipei Hsien, Taiwan, R. O. C.
TEL:886-2-86867781~4 FAX:886-2-86867780
<http://www.richbay.com.tw>



DRAWN BY

UNIT

mm



UNIT Q'TY

1

APPROVED BY

SCALE

1:1



TOLERANCE

X.XX±0.1
XX.XX±0.2
XXX.XX±0.3

ID NO

220929A03

DESCRIPTION

PRODUCT NO.

R-3013S(01)

REV

INTERIM NO.

NEW NO.

D