




SECTION P-P



RECOMMENDED PCB LAYOUT

DIMENSION

Dim A	NX7.62
Dim B	(N-1)X7.62
Dim C	(N-1)X7.62

N= Number of poles

Poles	Tolerance
2P-6P	±0.20
7P-12P	±0.30
13P-16P	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	01/26'07	Soldering temperature changed from 245° to 250°	Tony
△	04/08'09	Add TUV standard	Jacke
△	04/08'09	Add the tolerance table	Jacke
△	2009.10.21	The material is changed from Brass to Copper	Jacke
△	2010.12.08	The design is changed	Chen Bo
△	2011.08.09	The Dim C & dimension 7.62 are added	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ③ Male contact pin : Copper Tin plated
- Item ④ Terminal (housing): Thermoplastic (UL94V-0)

Electrical: cULus TUV

- Voltage rating: 300V 750V
- Current rating: 20A 15A
- Withstanding Voltage: 1.6 KV 6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus TUV
- Critical dimension: ▽

OQ xx 0 1 x 0 xxxx G

No. OF POLES
02: 2 POLES
:
16: 16 POLES

COLOR

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green(RAL6018/U)

G: Pb<40000ppm
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	OQ 7.62mm 180° /Close Series 2p-16p						
PART NO.	OQxx01x0xxxxG			DWG NO.	80Q0302		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
	Shi Jun 2011.08.10	Aaron 2011.08.09	Chen Bo 2010.12.08			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
						REV.: H	X.XX ±0.10
				SHEET: 01/01			X° ±1°