








PANEL CUT-OUT



XX	A
10	1.0
15	1.5
20	2.0



SPECIFICATION: (SWITCH)

- Electrical rating : 6A 250VAC & 12A 125VAC [UL] 4(1)A 250VAC [VDE . ENEC10]
- Contact resistance : <20mΩ (Initial)
- Insulation resistance : 100MΩ (500VDC between open contacts)
- Dielectric strength : 1500V 1 minute

SPECIFICATION:

- Insulation Resistance: Over 100MΩ at 500V DC.
- Dielectric strength: 2000V AC 1 Minute.
- Body Material: Thermoplastic 94V-2~V-0.

Rating:AC 15A 250V	
Mark	Safety Regulation
	CULUS
Rating:AC 10A 250V	
Mark	Safety Regulation
	VDE
	ENEC
	CCC

富灣股份有限公司 RICH BAY COMPANY LTD. 台北縣樹林市東興街57號 NO. 57, Tung Hsing St., Shu-Lin Town, Taipei Hsien, Taiwan, R. O. C. TEL:886-2-86867781~4 FAX:886-2-86867780 http://www.richbay.com.tw		UNIT	UNIT	QTY	SCALE	TOLERANCE	PRODUCT NO.	R-3014S (01) XX	REV
		mm		1	1:1	X.XX±0.1 XX.XX±0.2 XXX.XX±0.3			
		RD	RD			ID NO	220929A09	INTERIM NO.	L
		111.09.29 吳勝霖	111.09.29 張育誠			DESCRIPTION		NEW NO.	