





RECOMMEND
PANEL CUT OUT

Thickness	L
1.5	32.2
2.0	32.4
2.5	32.6
3.0	32.8


SPECIFICATION:

1. Insulation Resistance: Over 100MW at 500V DC.
2. Dielectric strength: 2000V AC 1 Minute.
3. Body Material: Thermoplastic 94V-2~V-0.

Rating: AC 15A 250V	
Mark	Safety Regulation
	CULUS
Rating: AC 10A 250V	
Mark	Safety Regulation
	VDE
	ENEC



富灣股份有限公司
RICH BAY COMPANY LTD.
台北縣樹林市東興街57號
NO. 57, Tung Hsing St., Shu-Lin Town,
Taipei Hsien, Taiwan, R. O. C.
TEL: 886-2-86867781~4 FAX: 886-2-86867780
http://www.richbay.com.tw



DRAWN BY

UNIT

mm

UNIT QTY

1

SCALE

1:1

TOLERANCE

X.XX±0.1
XX.XX±0.2
XXX.XX±0.3

PRODUCT NO.

R-3016 (00)

REV

ID NO

210224A07

INTERIM NO.

P060118A06

D

DESCRIPTION

NEW NO.

