








PANEL CUT-OUT



SPECIFICATION: (SWITCH)

- ELECTRICAL RATING : 10A 125VAC & 16A 125VAC [UL.CUL]
1/3 HP 125/250VAC [UL.CUL]
10(4)A 250VAC [ENEC]
10(2)A 250VAC [ENEC]
- CIRCUIT : DPST ON-OFF. W/1amp DPST 4P
- CONTACT RESISTANCE : 30mΩ Max
- INSULATION RESISTANCE : DC 500V 100MΩ Min
- WITHSTAND VOLTAGE : AC 1500V 1 Minute


SPECIFICATION:

- INSULATION RESISTANCE: OVER 100MΩ 500V DC.
- DIELECTRIC STRENGTH: 2000V AC ONE MINUTE.
- Body Materil: Black Glass-Fiber Thermoplastic . UL 94V-2~0

Rating:AC 10A 250V	
Mark	Safety Regulation
	VDE
	ENEC
	CCC
Rating:AC 15A 250V	
Mark	Safety Regulation
	cULus



富灣股份有限公司
RICH BAY COMPANY LTD.
台北縣樹林市東興街57號
NO. 57, Tung Hsing St.,Shu-Lin Town,
Taipei Hsien, Taiwan, R. O. C.
TEL:886-2-86867781~4 FAX:886-2-86867780
http://www.richbay.com.tw



DRAWN BY

UNIT

mm

UNIT Q'TY

1

SCALE

1:1

TOLERANCE

X.XX±0.1
XX.XX±0.2
XXX.XX±0.3

PRODUCT NO.

R-301SN(79)

REV

ID NO

230711A01

INTERIM NO.

DESCRIPTION

NEW NO.

H

R D
112.07.11
李文彬

APPROVED BY

R D
112.07.11
張育誠