






PCB Layout
Top view

△
N=Number of Poles
Dim.P=(N-1)×5.08
Dim.L=N×5.08+1.6

Poles Dim.	1P-3P	4P-9P	10P-15P	16P-21P	22P-24P
Dim.L	±0.10	±0.15	±0.25	±0.35	±0.40
Dim.P	±0.10	±0.15	±0.20	±0.30	±0.35

SIGN	DATE	DESCRIPTION	APPROVER
△	11/10'12	update the drawing	Da cheng

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item A Terminal body: Thermoplastic (UL94V-0)
- Item B Terminal cover: Thermoplastic (UL94V-0)
- △ ● Item C Terminal lever: Thermoplastic (UL94V-0) Orange(RAL2011/P)
- Item D Contact pin : Brass. Tin Plated.
- Item E Spring clamp : Stainless steel

- Electrical: cULus
- Voltage rating: 300 V
 - Current rating: 15A
 - Wire range:
 - Solid wire(AWG): 14-28
 - Stranded wire(AWG): 14-28
 - Wire strip length: 11-12 mm
 - Withstanding Voltage: 1.6 KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 260°C ±5°C/5 Sec
 - APPROVAL:
 - Critical dimension: ▽

H9 xx 5 0 x 0 xxxx G

No. OF POLES
01: 1 POLES
02: 2 POLES
:
24: 24 POLES

Body Color
0: BLACK
3: Orange (RAL 2011/P)
5: GREEN (RAL 6018/T)
8: GREY (RAL 7004/P)

△ C: Multiple colors

RoHS compliant
(lead<4%) △
In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	H9 5.08mm Series							
PART NO.	H9xx50x0xxxxG				DWG NO.	8H90001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Da cheng 2011.11.10	Da cheng 2011.11.10				UNIT: mm	X. ±0.50
							SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV: B		X.XX ±0.10	
							X° ±1°	