







SIGN	DATE	DESCRIPTION	APPROVER
△	7/07'09	Electrical standard is changed from UL/cUL to cULus	Kind
△	7/07'09	Current rating changed from 8A to 10A	Kind
△	7/07'09	Operating tem. changed from -30°C~105°C to -40°C~115°C	Kind
△	7/07'09	Add VDE Certification	Kind
△	2/03'12	Add the Elevation view	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- (A) Terminal body(metal housing of double): Brass(CuZn),Ni plated
- (B) Terminal body(metal housing of single): Brass(CuZn),Ni plated
- (C) Terminal screw: Steel Zinc plating "-" slot type
- (D) Wire guard: Steeless steel
- (E) Insulator (lever): Thermoplastic (UL94V-0)
- (F) Insulator (housing): Thermoplastic (UL94V-0)


- △ 8 △ 5 Electrical cULus VDE
 - Voltage rating: 400VAC / 450VAC
- △ 6
 - Current rating: 10A / 24A
 - Wire range: 0.34~2.5mm²
 - Solid wire(AWG): 14-22
 - Stranded wire(AWG): 14-22
 - Torque(Lb-In): 3.5 /0.5
 - Screw: M3 /Nm
 - Wire strip length: 7-8mm
 - Withstanding Voltage: 1.8KV / 2.5KV
- △ 7
 - Operating temperature: -40°C to +115°C
 - Safety Approval: cULus VDE
 - Critical dimension: △

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TM - series 3 Poles				DWG NO.	8TM0001		
PART NO.	TM0319000000G				CUST NO.			
APPROVED	CHECKED	DESIGNED	DRAWN	Chen Bo 02/03'12		SHEET: 01/01		Tolerance
						UNIT: mm		X. ±0.50
						SCALE: NONE		X.X ±0.30
						REV.: G		X.XX ±0.10
								X° ±1°



ANYTEK				CUSTOMER COPY			
				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE		TM - series 5 Poles with handle					
PART NO.		TM0519000000G		DWG NO.		8TM0301	
APPROVED		CHECKED		DESIGNED		DRAWN	
						Tolerance	
						X. ±0.50	
						X.X ±0.30	
						X.XX ±0.10	
						X° ±1°	
		Chen Bo 02/03 12		SHEET: 01/01		UNIT: mm	
						SCALE: NONE	
						REV: H	