





RevNo	Revision Notes	Date	Checked
1	RoHS Compliant	052005	GC
2	Barrel center to end face dimension changed to .417"	071206	GC



RECOMMENDED
STRIP LENGTHS
M17/94-RG179



RoHS Compliant

MATERIAL

BODY	BRASS
BODY PLATING	GOLD
CONTACT	BERYLLIUM COPPER
CONTACT PLATING	GOLD
DIELECTRIC	TEFLON (PTFE)

75 Ohm IMPEDANCE
500V PEAK VOLTAGE RATING
TEMPERATURE RANGE: -55°C TO +155°C
INTERFACE DIMENSIONS SIMILAR TO MIL-C-39012

MILLIMETER WAVE TECHNOLOGIES
6501 W. FRYE ROAD, #23
CHANDLER, AZ 85226

SMB FEMALE RIGHT ANGLE
CRIMP CABLE END
for RG179 75 Ohm

Designed by N. JAIN	Checked by W. CANON	Approved by A. LEE	File name MWB-6018-G-179	TITLE MWB-6018-G-179	
TOLERANCES DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED DECIMALS ANGULAR .XX ± .02 ± .06 .XXX ± .005 ± .01 DO NOT SCALE THIS DRAWING		ALL DIMENSIONS ON THIS DRAWING ARE FOR REFERENCE PURPOSES ONLY AND ARE SUBJECT TO CHANGE.		REV. 2	Scale NONE
				DATE 040101	Sheet 1 of 1