

MATERIAL AND FINISH:
Insulator: PA66, UL-94V-0 rated
Contacts: Brass, Tin plated

ELECTRICAL SPECIFICATIONS:

Current rating: 10 A





Voltage rating: 250 VAC

Current rating: 15 A




Voltage rating: 250 VAC



RoHS
COMPLIANT



SEE DETAIL A
REPLACE WITH
CORRESPONDING
PANEL THICKNESS



DETAIL A

RECOMMENDED
PANEL CUTOUT



P/N	A	MAX. PANEL THICKNESS	XX
43R03-3121-120	1.50	1.2	1.20
43R03-3121-150	1.80	1.5	1.5
43R03-3121-200	2.35	2.0	2.0
43R03-3121-250	2.85	2.5	2.5
43R03-3121-300	3.45	3.0	3.0

ADDITIONAL PANEL THICKNESS
AVAILABLE ON REQUEST

REVISIONS		CHANGE	CHK	CHK	APPR
REV	DATE	DESCRIPTION	BY	TD	PB
A	8/15/01	RE-TOOLED	GQ	TD	PB
B	7/13/06	ADD 1.27 PANEL THICKNESS	PB		
C	12/12/11	RE-TOOLED	PB		
D	2/18/20	24.40 WAS 24.0 REV. PANEL CUTOUT	PB		
E	12/10/20	-120 WAS -127	PB		

TOLERANCE UNLESS OTHERWISE SPECIFIED	
X	± 1
X.X	± 0.4
X.XX	± 0.20
DRAWN BY	GQ
CHECK BY	TD
APPR BY	PB
DATE:	08/15/01
DATE:	8/17/01
DATE:	8/17/01

Power Dynamics, Inc.	
Phone: 973 560-0019 Whippary, New Jersey Fax: 973 560-0076	
PART: IEC 60320 C13 APPL. OUTLET; QC TERMINALS; SNAP-IN	
PART #: 43R03-3121-XXX	
SIZE: A	SHEET 1 of 1
SCALE: NTS	REV: E
ALL DIMENSIONS FOR REFERENCE ONLY DIMENSIONS ARE IN MILLIMETERS	