

TIF®800HP Series thermally conductive interface materials are applied to fill the air gaps between the heating elements and the heat dissipation fins or the metal base. Their flexibility and elasticity make them suited to coat very uneven surfaces. Heat can transmit to the metal housing or dissipation plate from the heating elements or even the entire PCB, which effectively enhances the efficiency and life-time of the heat-generating electronic components.

Typical Properties of TIF®800HP Series

Property	Value	Test method
Color	Gray	Visual
Construction	Ceramic filled silicone elastomer	-
Thickness range	0.030"(0.75mm)~0.200" (5.0mm)	ASTM D374
Hardness (Shore 00 Thickness ≥ 0.75mm)	45	ASTM 2240
Hardness (Shore 00 Thickness < 0.75mm)	65	ASTM 2240
Density (g/cm³)	3.55	ASTM D792
Continuous Use Temp (°C)	-40~200	Ziitek Test Method
Dielectric Breakdown Voltage (T=1.0mm, Vac)	≥5500	ASTM D149
Dielectric Constant@1MHz	4.5	ASTM D150
Volume Resistivity	≥1.0X10 ¹² Ohm-cm	ASTM D257
Thermal Conductivity (W/mK)	12.0	ASTM D5470
	12.0	ISO22007-2.2
Flame Rating	V-0	UL 94


Features

- » Good thermal conductivity
- » Naturally tacky needing no further adhesive coating
- » Soft and Compressible for low stress applications
- » Available in varies thickness


Application

- » Cooling components to the chassis of frame
- » Set Top Box
- » Car Battery & Power Supply
- » Charging Pile
- » LED TV/ Lighting
- » Graphics Card Thermal Module

Pressure. vs. Thermal Resistance



Pressure. vs. Compression Ratio



Product Thicknesses: 0.030-inch to 0.200-inch (0.75mm to 5.0mm) **Product Sizes:** 8" x 16" (203mm x 406mm)

Individual die cut shapes and custom thickness can be supplied. Please contact us for confirming

Safe disposal method does not require special protection. The storage condition is low temperature and dry, away from open fire and away from direct sunlight. For detailed method, please refer to the product material safety data sheet.

[Thermally Conductive Materials](#) [Thermally Conductive Plastics](#) [Heat Generating Materials](#) [Shielding Materials](#) [Foaming Silica Gel](#) [Die-Cutting Products](#)

Canada

TEL: +001-604-2998559
E-mail: frances@ziitek.com.tw
[Http://www.thermazig.com](http://www.thermazig.com)

Taiwan

TEL: +886-2-22771007
E-mail: frances@ziitek.com.tw
[Http://www.ziitek.com.tw](http://www.ziitek.com.tw)

Dongguan

TEL: +86-769-38801208
E-mail: frances@ziitek.com.tw
[Http://www.ziitek.com.cn](http://www.ziitek.com.cn)

Kunshan

TEL: +86-512-57816297
E-mail: kelvin@ziitek.com
[Http://www.ziitek.com.cn](http://www.ziitek.com.cn)

Changsha

TEL: +86-731-86949836
E-mail: jor@ziitek.com
[Http://www.ziitek.com.cn](http://www.ziitek.com.cn)

The information and statements herein are believed to be reliable but are not to be construed as a warranty or representation for which we assume legal responsibility. Users should undertake sufficient verification and testing to determine the suitability for their own particular purpose of any information or products referred to herein.