

SIGN	DATE	DESCRIPTION	APPROVER
△	04/07'09	wire range and operating temperature are changed	Jacke
△	04/07'09	Add UL standard	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item a Clamp: Brass (CuZn). Ni plating
- Item b Terminal screw:Steel Zinc plating “-”slot type
- Item c Female contact: PhBz (CuSn) Tin plated
- Item d Terminal(housing):Thermoplastic(UL94V-0)

Electrical

- Voltage rating:300V
- Current rating:10A
- Wire range:
- Solid wire(AWG):14-26
- Stranded wire(AWG):14-26
- Torque(Lb-In):3.5
- Screw:M3
- Wire strip length:6-7mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C
- Safety APPROVAL: 

VG xx 01 x 0 xxxx G

02 2 CONTACTS	0 Black (RAL9005)	RoHS
03 3 CONTACTS	2 Red (RAL3001/D)	Pb<40,000ppm
...	3 Orange(RAL2011/P)	0000:"@”Logo (Standard)
24 24 CONTACTS	4 Yellow(RAL1018/A)	000A:"ANYTEK”Logo
	5 Green(RAL6018/T)	Any special item by
	6 Blue (RAL5015/A)	customer request,
	8 Grey(RAL7035/D)	please contact sales
		department.

N = Number of poles
Dim A=Nx5.0
Dim B=(N-1)x5.0

	Dim A	Dim B
2-6p	±0.15	±0.10
7-12p	±0.20	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30

ANYTEK				CUSTOMER COPY			
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD							
TITLE	VG -5.0mm Series						
PART NO.	VGxx01x0xxxxG			DWG NO.	8VG0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Jacke 2009.04.08	Jacke 2009.04.08			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01		REV.: E	X.XX ±0.10
							X° ±1°