

REVISIONS		
LTR	DESCRIPTION	DATE
N	REVISED PER ECO-13-015722	10/07/13

- NOTES:
- ALL DIMENSIONS ARE IN INCHES
[MILLIMETERS]
 - DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:
 - AS SUPPLIED
 - AFTER UNRESTRICTED RECOVERY
 - TOLERANCES FOR MARKED PARTS TO BE
+ .002/- .004
[+0.05/-0.10]
 - SERRATIONS TO MATE WITH SERRATIONS IN
BOOTS AND TRANSITIONS.




TABLE OF DIMENSIONS											
PART NUMBER	H	J	P	R	HW	JW	PART NUMBER	H	J	P	R
202B211	.329 [8.36]	.188 [4.78]	1.00 [25.4]	.50 [12.7]	.04 [1.0]	.016 ± .008 [0.40 ± 0.20]	202B261	.811 [20.6]	.610 [15.50]	1.00 [25.4]	.50 [12.7]
202B221	.421 [10.7]	.264* [6.70]	1.00 [25.4]	.50 [12.7]	.04 [1.0]	.016 ± .008 [0.40 ± 0.20]	202B272	.941 [23.9]	.721 [18.30]	1.00 [25.4]	.50 [12.7]
202B231	.524 [13.3]	.354* [9.00]	1.00 [25.4]	.50 [12.7]	.04 [1.0]	.016 ± .008 [0.40 ± 0.20]	202B282	1.087 [27.6]	.850* [21.60]	1.00 [25.4]	.50 [12.7]
202B241	.591 [15.0]	.431 [10.95]	1.00 [25.4]	.50 [12.7]	.04 [1.0]	.030 ± .010 [0.76 ± 0.25]	202B292	1.213 [30.8]	.978 [24.85]	1.00 [25.4]	.50 [12.7]
202B251	.658 [16.7]	.492* [12.50]	1.00 [25.4]	.50 [12.7]	.04 [1.0]	.032 ± .010 [0.80 ± 0.25]	202B302	1.532 [38.9]	1.177 [29.90]	1.00 [25.4]	.50 [12.7]

ORDERING INFORMATION

BASE PART NUMBER _____

MATERIAL DASH NUMBER _____

(SEE COMPATABILITY CHART)

MODIFICATION NUMBER _____

(IF NECESSARY, SEE FRONT OF SOD BINDER FOR A COMPLETE LIST)

ADHESIVE SLASH NUMBER _____

(IF NECESSARY, SEE COMPATABILITY CHART)

COMPATIBILITY CHART			
MATERIAL DASH NO.	MATERIAL DESCRIPTION	COATING SLASH NUMBER	COATING S NUMBER
-13	Nylon, Glass Filled		

IF THIS DOCUMENT IS PRINTED IT BECOMES UNCONTROLLED.
CHECK FOR THE LATEST REVISION.

Raychem Molded Parts
CUSTOMER DRAWING

TE Connectivity

STE

SLEEVE, CONDUIT

TITLE

SIZE CODE LTR NO DWG NO

B 06090 202B211thru 302

DO NOT SCALE THIS DRAWING

SHEET 1 OF 1