






P.C.B Layout

DimL=N/2×3.5
DimP=(N/2-1)×3.5
DimK=(N/2-1)×3.5

N=Number of poles

POLES	Dim. Tol	Dim.L	Dim.P
2x2p-2x6p		±0.15	±0.10
2x7p-2x12p		±0.25	±0.20
2x13p-2x18p		±0.35	±0.30
2x19p-2x24p		±0.40	±0.35

SIGN	DATE	DESCRIPTION	APPROVER
△	04/25`11	Material is changed	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			


Material:

- Item ③ Terminal housing: PA66 (UL94V-0)
- △ Item ⑤ Male contact pin: Brass, Tin plated

Electrical:

cULus

- Voltage rating: 150V
- Current rating: 7A
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:



SECTION A-A

V X xx 1 0 x 0 xxxx G

No of plose
04 2x2 CONTACTS
06 3x2 CONTACTS
...
48 24x2 CONTACTS

0 Black
3 Orange
5 Green
6 Blue
8 Grey

RoHS
Pb<40,000ppm
0000 Standard @ Logo
000A Standard ANY Logo
Any special item by customer request, please contact sales department.

ANYTEK

INSPECTION COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VX 3.5mm Series Open type Vertical					
PART NO.		VXxx10x0xxxxG		DWG NO.	8VX0006		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Runner 2011.04.25	Chen Bo 2011.04.25		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01		REV: C	X.XX ±0.10
							X° ±1°