


Push Locking Connection



● Features:


- Reliable Quick Connection
- Key Lock structure
- Optional Shielding function
- Up to IP68 rating

Patented
product





- WK16 Series IP67
- WK20 Series IP68
- Lock the hook tightly




★ Contact can be male or female


Material and spec

Specifications	WK16	WK20
Coupling	Push lock	
Shell	PPE / Zinc alloy	
Insert material	PPS, PBT max temperature 260 °C	
Contact material	Brass	
Contact plating	Gold Plating	
Termination	Solder: Ø1mm, Ø1.5mm contact	Solder: Ø1mm, Ø2mm, Ø3mm contact Screw: Ø3mm contact Crimp
Key lock	Without	With
IP rating	IP67	IP68
Mating cycle	500	
Temperature range	-40℃ ~ +105℃	
Insulation resistance	2000 MΩ	

● WK Series




WK Series Mating diagram







● Square flange receptacle: Z IP68




● Front-nut-mount receptacle: ZMQ IP68




● Round flange receptacle: ZM IP68




● In-line shielded receptacle with metal clamping-nut: ZEP IP68




● Plug with plastic clamping-nut: TE IP68



● In-line receptacle with plastic clamping-nut: ZE IP68



● Shielded Plug with metal clamping-nut: TEP IP68



Solder contact spec

WK20	2	3	4	5	5B	5C	6	6B	7	8	9	12	15
Male contact face view													
Rated current (A)	30	30	30	30	30 5	15	25 5	30 5	15	10	5	5	5
Contact diameter (mm)	ø3X2	ø3X3	ø3X4	ø3X5	ø3X2 ø1X3	ø2X5	ø2.5X4 ø1X2	ø3X2 ø1X4	ø2X7	ø1.5X8	ø1X9	ø1X12	ø1X15
Rated voltage (AC.V)	500	500	500	500	500	500	500	500	500	500	400	400	400
Test voltage(AC.V) 1 min	1500	1500	1500	1500	1500	1500	1500	1500	1500	1500	1200	1200	1200
Contact resistance (mΩ)	1	1	1	1	1 5	2.5	1 5	1 5	2.5	2.5	5	5	5
Wire size for solder (mm² / AWG)	≦4/11	≦4/11	≦4/11	≦4/11	≦4/11 ≦0.75/18	≦2/14	≦4/11 ≦0.75/18	4/11 ≦0.75/18	≦2 / 14	≦2 / 14	<0.75/18	<0.75/18	<0.75/18


Crimp contact spec

SF20, SA20, SP21, SY21, WK20, WS20, WF20, WY20, WP20	1	2	3	4	5	7	7B	8
Male contact face view								
Rated current (A)	100	25	25	25	10	10	5	5
Contact diameter(mm)	Ø5.5X1	Ø2.5X2	Ø2.5X3	Ø2.5X4	Ø1.5X5	Ø1.5X7	Ø1X7	Ø1X8
Rated voltage (AC.V)	500	500	500	500	500	500	400	400
Test voltage(AC.V) 1 min	1500	1500	1500	1500	1500	1500	1200	1200
Contact resistance(mΩ)	0.3	1	1	1	2.5	2.5	5	5
Insulation resistance(MΩ)	2000	2000	2000	2000	2000	2000	2000	2000

Crimp contact

5A Crimp contact

- ※ Contact diameter: Ø1
- ※ Material: Brass with gold plating
- ※ Contact resistance: 5mΩ




5A Male crimp contact					For SF, SA, SP, SY, WP, WS/ WF/ WY16-28
Wire size	Stripping length	Male crimp contact p/n	Crimping tool p/n	Removal tool p/n	
0.20-0.52mm ² AWG 24-20	5.5mm	YJ1-17-0.52AU-C OC YJ1-17-0.52AU	CT-P20/28	RT-1.0	

5A Female crimp contact					For SF, SA, SP, SY, WP, WS/ WF/ WY16-28
Wire size	Stripping length	Female crimp contact p/n	Crimping tool p/n	Removal tool p/n	
0.20-0.52mm ² AWG 24-20	5.5mm	YK1-17-0.52AU-C OC YK1-17-0.52AU	CTW-0.14/4	RT-1.0	

10A Crimp contact

- ※ Contact diameter: Ø1.5
- ※ Material: Brass with gold plating
- ※ Contact resistance: 2.5mΩ




10A Male crimp contact					For SF, SA, SP, SY, WP, WS/ WF/ WY16-28
Wire size	Stripping length	Male crimp contact p/n	Crimping tool p/n	Removal tool p/n	
0.14-0.37mm ² AWG 26-22	8mm	YJ1.5-21.4-0.37AU	CTW-0.14/4	RT-1.5	
0.5mm ² AWG 20	8mm	YJ1.5-21.4-0.5AU	CTW-0.14/4	RT-1.5	
0.75-1.0mm ² AWG 18	8mm	YJ1.5-21.4-1.0AU	CTW-0.14/4	RT-1.5	
1.5mm ² AWG 16	8mm	YJ1.5-21.4-1.5AU	CTW-0.14/4	RT-1.5	
2.5mm ² AWG 14	8mm	YJ1.5-21.4-2.5AU	CTW-0.14/4	RT-1.5	

10A Female crimp contact					For SF, SA, SP, SY, WP, WS/ WF/ WY16-28
Wire size	Stripping length	Female crimp contact p/n	Crimping tool p/n	Removal tool p/n	
0.14-0.37mm ² AWG 26-22	8mm	YK1.5-20.4-0.37AU	CTW-0.14/4	RT-1.5	
0.5mm ² AWG 20	8mm	YK1.5-20.4-0.5AU	CTW-0.14/4	RT-1.5	
0.75-1.0mm ² AWG 18	8mm	YK1.5-20.4-1.0AU	CTW-0.14/4	RT-1.5	
1.5mm ² AWG 16	8mm	YK1.5-20.4-1.5AU	CTW-0.14/4	RT-1.5	
2.5mm ² AWG 14	8mm	YK1.5-20.4-2.5AU	CTW-0.14/4	RT-1.5	

25A Crimp contact

- ※ Contact diameter: Ø2.5
- ※ Material: Brass with gold plating
- ※ Contact resistance: 1mΩ




25A Male crimp contact					For SF, SA, SP, SY, WP, WS/ WF/ WY16-28
Wire size	Stripping length	Male crimp contact p/n	Crimping tool p/n	Removal tool p/n	
0.75-1.0mm ² AWG 18	8mm	YJ2.5-21.4-1.0AU	CTW-0.14/4	RT-2.5	
1.5mm ² AWG 16	8mm	YJ2.5-21.4-1.5AU	CTW-0.14/4	RT-2.5	
2.5mm ² AWG 14	8mm	YJ2.5-21.4-2.5AU	CTW-0.14/4	RT-2.5	
4.0mm ² AWG 12	8mm	YJ2.5-21.4-4.0AU	CTW-0.14/4	RT-2.5	

Crimp contact

25A Crimp contact

- ※ Contact diameter: Ø2.5
- ※ Material: Brass with gold plating
- ※ Contact resistance:1mΩ



25A Female crimp contact				For SF, SA, SP, SY, WP, WS/WF/WY16-28	
Wire size		Stripping length	Female crimp contact p/n	Crimping tool p/n	Removal tool p/n
0.75-1.0mm ²	AWG 18	8mm	YK2.5-20-1.0AU	CTW-0.14/4	RT-2.5
1.5mm ²	AWG 16	8mm	YK2.5-20-1.5AU	CTW-0.14/4	RT-2.5
2.5mm ²	AWG 14	8mm	YK2.5-20-2.5AU	CTW-0.14/4	RT-2.5
4.0mm ²	AWG 12	8mm	YK2.5-20-4.0AU	CTW-0.14/4	RT-2.5

Crimp tool

For crimping the male / female contacts



Part number	Crimping wire range
YQK-70	4-70mm ² AWG 11-2/0

Crimp tool and Removal tool

Crimp tool

For crimping the male / female contacts



Part number	Crimping wire range
CT-P20/28	0.08-0.52mm ² AWG 28-20
CTW-0.14/4	0.14-4mm ² AWG 26-12

Part number	Crimping wire range
CT-4/10	4-10mm ² AWG 11-7
CT-0.14/4	0.14-4mm ² AWG 26-12

Removal tool

For taking out male / female contacts



Part number	Removal range
RT-1.0	5A Male / Female crimp contact
RT-1.5	10A Male / Female crimp contact
RT-2.5	25A Male / Female crimp contact
RT-3.5	50A Male / Female crimp contact

Screw contact spec

SP21, SY21, WP20, WK20	2	3	4	5
Male contact face view				
Rated current (A)	10	10	10	10
Contact diameter(mm)	ø3×2	ø3×3	ø3×4	ø3×5
Rated voltage (AC.V)	500	500	500	500
Test voltage(AC.V) 1 min	1500	1500	1500	1500
Contact resistance (mΩ)	1	1	1	1
Wire size (mm² / AWG)	≤1.5/15	≤1.5/15	≤1.5/15	≤1.5/15

WK Series

