

THIS DOCUMENT CONTAINS PROPRIETARY DATA OF POLARIS INDUSTRIAL ENTERPRISES INC. NO DISCLOSURE, REPRODUCTION, OR USE OF ANY PART THERE OF MAY BE MADE EXCEPT BY WRITTEN PERMISSION.

REV.	BY	DATE	APPROVL.	P/N
C	DMS	1-12-98	BT	LCP15 ADDED LCP15" T" CALLOUT.

ELECTRICAL
RESISTANCE RANGE ----- SEE CHART
RESISTANCE TOLERANCE ----- ±10%
LINEARITY, INDEPENDENT ----- SEE CHART
RESOLUTION ----- ESSENTIALLY INFINITE
MINIMUM RESISTANCE ----- 1 OHM OR 0.1%
STROKE ----- SEE CHART
OUTPUT SMOOTHNESS ----- <0.1% AGAINST INPUT VOLTAGE
POWER RATING @40°C ----- SEE CHART
INSULATION RESISTANCE ----- 1000 MEGOHMS AT 1000 VDC
DIELECTRIC STRENGTH ----- 1 MIN @ 1000VAC
CONTACT RESIS. VARIATION ----- BELOW 2% C.R.V.


MECHANICAL
STROKE ----- SEE CHART
STOP STRENGTH ----- 2.2 LBS. MIN.
FRICTION ----- BELOW 30 GRAMS
LIFE ----- 20,000,000 STROKES

ENVIRONMENTAL
OPERATING TEMPERATURE RANGE -- 30°C TO 105°C
TEMPERATURE COEFFICIENT ----- 400 PPM/°C
VIBRATION ----- 10Hz TO 2,000Hz 15G
MOISTURE RESISTANCE ----- 40°C 95%RH 120 HOURS
SHOCK ----- 50G 11ms

MATERIALS
HOUSING ----- THERMO-SETTING PLASTIC
SHAFT ----- STAINLESS STEEL
TERMINALS ----- GOLD PLATED
RESISTIVE ELEMENT ----- CONDUCTIVE PLASTIC

NON-STANDARD OPTIONS
SPECIAL RESIS. & LINEARITY ----- NOTE: TERMINALS ACCEPT AMP#110
MACHINED SHAFTS ----- CONNECTORS.
SPRING RETURN

SCHEMATIC



DIMENSION TABLE

DASH NO.	APPROX WEIGHT	MECHANICAL STROKE +.080-.000	ELEC. STROKE ±.020	RESIS. RANGE	LINEARITY STANDARD PRECISION	'Y'	'X'	POWER RATING
-10	1 OZ.	.394	.394	500/10K	± 2% ± 1%	1.46	.787	0.2 WATTS
-15	1 OZ.	.590	.590	500/10K	± 1% ± 0.5%	1.46	.787	0.3 WATTS
-20	1 OZ.	.787	.787	500/10K	1% 0.5%	2.05	1.378	0.4 WATTS
-30	1 OZ.	1.181	1.181	500/10K	1% 0.5%	2.05	1.378	0.5 WATTS


TOLERANCES

XX - +/- .010" FRACT. - +/- 1/64"
XXX - +/- .005" ANGLES - +/- 1/2"
ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

MODEL NO.'S.

SHAFT STYLES

LCP15P-(STROKE)-(RES.)	(P)	PLAIN
LCP15C-	"	CHAMFERED
LCP15S-	"	SPRING RETURN (INTERNAL)
LCP15T-	"	THREADED



FTI SYSTEMS
CARLSBAD
CALIFORNIA

TITLE
LINEAR MOTION
POTENTIOMETER

PART NO.

LCP15