






# ELECTRICAL

ELECTRICAL ACCESSORIES																																																																									
Product		Features		Accessory For																																																																					
<div><div>P0200-19</div><div>Heat Sink Compound</div><div>2 grams</div><div>P0200-20</div><div>Heat Sink Compound</div><div>100 grams</div></div> <div></div>		<div>Single package/container of heat sink compound consisting of primarily zinc oxide and having a 12 month shelf life (EOD date on the label). P0200-19 mounts one high current, plated 2 x 2 in. (50.8 x 50.8 mm) timer or flasher. P0200-20 mounts 50+ units.</div>		<div>Any 2 x 2 in. (50.8 x 50.8 mm) plated timer or flasher.</div>																																																																					
<div><div>P1015-18</div><div>Quick Connect Screw Adaptor</div></div> <div></div>		<div>Screw adaptor terminal designed for use with all modules with 0.25 in. (6.35 mm) male quick connect terminals. Screw terminal accepts ring or spade terminals.</div>		<div>Modules with 0.25 in. (6.35 mm) male quick connect terminals. Consult the individual datasheet to determine compatibility.</div>																																																																					
<div><div>P1015-13</div><div>P1015-64</div><div>P1015-14</div><div>Female Quick Connect Terminals</div></div> <div></div>		<div>These 0.25 in. (6.35 mm) female terminals are constructed with an insulator barrel to provide strain relief.</div>		<div>Consult individual datasheet to determine compatibility.</div>																																																																					
<div><div>P0400</div><div>Time Adjustment Dials</div></div> <div></div>		<div>Dials for use with remote Versa-Pot and panel mounted Mini-Pot. Reverse screen printed on clear plastic to avoid damage to printed image.</div>		<div><div>P1004-9</div><div>P1004-13</div><div>P1004-95</div><div>P1004-10</div><div>P1004-16</div><div>P1004-12</div><div>P1004-31</div></div>																																																																					
<table><thead><tr><th>PART NUMBER</th><th>RANGE</th><th>INCREMENTS</th></tr></thead><tbody><tr><td>P0400-12</td><td>0.05 - 1s</td><td>0.1s</td></tr><tr><td>P0400-86</td><td>0.1 - 10m</td><td>1m</td></tr><tr><td>P0400-82</td><td>0.1 - 10s</td><td>1s</td></tr><tr><td>P0400-17</td><td>1 - 30s</td><td>5s</td></tr><tr><td>P0400-83</td><td>1 - 60s</td><td>10s</td></tr><tr><td>P0400-27</td><td>0 - 10</td><td>MRD*</td></tr></tbody></table> <div>*Multiplier Reference Dial</div>						PART NUMBER	RANGE	INCREMENTS	P0400-12	0.05 - 1s	0.1s	P0400-86	0.1 - 10m	1m	P0400-82	0.1 - 10s	1s	P0400-17	1 - 30s	5s	P0400-83	1 - 60s	10s	P0400-27	0 - 10	MRD*																																															
PART NUMBER	RANGE	INCREMENTS																																																																							
P0400-12	0.05 - 1s	0.1s																																																																							
P0400-86	0.1 - 10m	1m																																																																							
P0400-82	0.1 - 10s	1s																																																																							
P0400-17	1 - 30s	5s																																																																							
P0400-83	1 - 60s	10s																																																																							
P0400-27	0 - 10	MRD*																																																																							
<div><div>VTPXX</div><div>VTP</div><div></div></div>		<div>The VTP Series mounts on modules with in-line adjustment terminals. Rated at 0.25W at 55°C. Available in resistance values from 5K Ω to 5MΩ</div>		<div><div>Series: TAC1</div><div>TS2</div><div>THD7</div><div>TS4</div><div>THDM</div><div>TS6</div><div>TS1</div><div>TSD7</div></div>																																																																					
<table><thead><tr><th>PART NUMBER</th><th>R<sub>T</sub> VALUE</th><th>RANGE</th><th>PART NUMBER</th><th>R<sub>T</sub> VALUE</th><th>RANGE</th></tr></thead><tbody><tr><td>VTP0E</td><td>250kΩ</td><td>0.5 - 20s</td><td>VTP3L</td><td>2MΩ</td><td>0.1 - 4m</td></tr><tr><td>VTP1B</td><td>0.5MΩ</td><td>0.05 - 3s</td><td>VTP4B</td><td>3MΩ</td><td>0.05 - 3s</td></tr><tr><td>VTP1C</td><td>0.5MΩ</td><td>0.1 - 10s</td><td>VTP4F</td><td>3MΩ</td><td>0.5 - 60s</td></tr><tr><td>VTP1D</td><td>0.5MΩ</td><td>0.5 - 10s</td><td>VTP4J</td><td>3MΩ</td><td>2 - 180s</td></tr><tr><td>VTP2A</td><td>1MΩ</td><td>0.05 - 1s</td><td>VTP4P</td><td>3MΩ</td><td>1 - 100m</td></tr><tr><td>VTP2C</td><td>1MΩ</td><td>0.1 - 10s</td><td>VTP5G</td><td>5MΩ</td><td>1 - 100s</td></tr><tr><td>VTP2E</td><td>1MΩ</td><td>0.5 - 20s</td><td>VTP5K</td><td>5MΩ</td><td>10 - 1000s</td></tr><tr><td>VTP2F</td><td>1MΩ</td><td>0.5 - 60s</td><td>VTP5N</td><td>5MΩ</td><td>0.1 - 10m</td></tr><tr><td>VTP2J</td><td>1MΩ</td><td>2 - 180s</td><td>VTP5P</td><td>5MΩ</td><td>1 - 100m</td></tr><tr><td>VTP2P</td><td>1MΩ</td><td>1 - 100m</td><td>VTPDF</td><td>50KΩ</td><td>0.5 - 60s</td></tr><tr><td>VTP3B</td><td>2MΩ</td><td>0.05 - 3s</td><td></td><td></td><td></td></tr></tbody></table>		PART NUMBER	R <sub>T</sub> VALUE			RANGE	PART NUMBER	R <sub>T</sub> VALUE	RANGE	VTP0E	250kΩ	0.5 - 20s	VTP3L	2MΩ	0.1 - 4m	VTP1B	0.5MΩ	0.05 - 3s	VTP4B	3MΩ	0.05 - 3s	VTP1C	0.5MΩ	0.1 - 10s	VTP4F	3MΩ	0.5 - 60s	VTP1D	0.5MΩ	0.5 - 10s	VTP4J	3MΩ	2 - 180s	VTP2A	1MΩ	0.05 - 1s	VTP4P	3MΩ	1 - 100m	VTP2C	1MΩ	0.1 - 10s	VTP5G	5MΩ	1 - 100s	VTP2E	1MΩ	0.5 - 20s	VTP5K	5MΩ	10 - 1000s	VTP2F	1MΩ	0.5 - 60s	VTP5N	5MΩ	0.1 - 10m	VTP2J	1MΩ	2 - 180s	VTP5P	5MΩ	1 - 100m	VTP2P	1MΩ	1 - 100m	VTPDF	50KΩ	0.5 - 60s	VTP3B	2MΩ	0.05 - 3s	
PART NUMBER	R <sub>T</sub> VALUE	RANGE	PART NUMBER	R <sub>T</sub> VALUE	RANGE																																																																				
VTP0E	250kΩ	0.5 - 20s	VTP3L	2MΩ	0.1 - 4m																																																																				
VTP1B	0.5MΩ	0.05 - 3s	VTP4B	3MΩ	0.05 - 3s																																																																				
VTP1C	0.5MΩ	0.1 - 10s	VTP4F	3MΩ	0.5 - 60s																																																																				
VTP1D	0.5MΩ	0.5 - 10s	VTP4J	3MΩ	2 - 180s																																																																				
VTP2A	1MΩ	0.05 - 1s	VTP4P	3MΩ	1 - 100m																																																																				
VTP2C	1MΩ	0.1 - 10s	VTP5G	5MΩ	1 - 100s																																																																				
VTP2E	1MΩ	0.5 - 20s	VTP5K	5MΩ	10 - 1000s																																																																				
VTP2F	1MΩ	0.5 - 60s	VTP5N	5MΩ	0.1 - 10m																																																																				
VTP2J	1MΩ	2 - 180s	VTP5P	5MΩ	1 - 100m																																																																				
VTP2P	1MΩ	1 - 100m	VTPDF	50KΩ	0.5 - 60s																																																																				
VTP3B	2MΩ	0.05 - 3s																																																																							