

Cat6 Hi-Flex PUR Jacket, Double Shielded, 4 Pr. Str. 26 AWG, Red, Booted Cable, 150ft.

**RoHS
Compliant**

Stock No.: CAT6-1504P-SSTP

FEATURES

- Strain Relief
- SSTP
- 26 AWG
- Stranded Copper




Product Description

This line of outdoor/industrial cables are designed for extreme applications where rugged, shielded, high-flex cables are required. They feature ultra-violet resistant jackets. These jackets are pressure extruded over the cable core, effectively locking the twisted pairs in place. This provides very stable electrical performance, even when the cables are impacted, bent or repeatedly flexed.



General Specifications

Attribute	Value
Terminated/Unterminated	Terminated
Connector Type	RJ45
Cable Type	Ethernet
Length	150.00' (45.72m)
Gauge	26 AWG
Conductor	Bare Copper
Shield/Unshielded	Double Shielded
Voltage Rating	30V
1.0 - 550MHz Impedance (Ω)	100 \pm 15
Maximum Operating Frequency	550MHz
Operating & Storage Temp.	-40°C to 60°C -40°F to 140°F
Installation Temp.	-20°C to 60°C -4°F to 140°F
Jacket Color	PUR (polyurethane), Red

Product Drawing



INK MARKING: Aein bei ke® E503807 AWM 20937(Cat 6 S/FTP) 4×2×26AWG 80°C 30V AWM I/II A/B 4×2×26AWG 80°C 30V FT2 SHANGHAI AEIN xxx M



- Note:
1. 100% Open/Short/Intermittent test.
 2. Data transfer rate: Pass the TIA CAT6 Channel test.
 3. Material meets RoHS 2.0

Dimensions: Millimeters (Inches)

Part Number Table

PART NUMBER	DESCRIPTION
CAT6-0504P-SSTP	Cat6 Hi-Flex PUR Jacket, Double Shielded, 4 Pr. Str. 26 AWG, Red, Booted Cable, 50ft.
CAT6-0754P-SSTP	Cat6 Hi-Flex PUR Jacket, Double Shielded, 4 Pr. Str. 26 AWG, Red, Booted Cable, 75ft.
CAT6-1004P-SSTP	Cat6 Hi-Flex PUR Jacket, Double Shielded, 4 Pr. Str. 26 AWG, Red, Booted Cable, 100ft.
CAT6-1504P-SSTP	Cat6 Hi-Flex PUR Jacket, Double Shielded, 4 Pr. Str. 26 AWG, Red, Booted Cable, 150ft.
CAT6-2004P-SSTP	Cat6 Hi-Flex PUR Jacket, Double Shielded, 4 Pr. Str. 26 AWG, Red, Booted Cable, 200ft.

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.