








PANEL CUT-OUT



XX	A
1.5	1.6
1.7	1.8
2.0	2.1
2.5	2.6



SPECIFICATION:

1. INSULATION RESISTANCE: OVER 100M 500V DC.
2. DIELECTRIC STRENGTH: 2000V AC ONE MINUTE. Ω
3. Body Materil: Black Glass-Fiber Thermoplastic . UL 94V-2~0

SPECIFICATION: (SWITCH)

1. ELECTRICAL RATING

: 10A 125VAC & 16A 125VAC [UL.CUL]
 1/3 HP 125/250VAC [UL.CUL]
 10(4)A 250VAC [ENEC]
 10(2)A 250VAC [ENEC]

2. CIRCUIT

: DPST ON-OFF. W/1amp DPST 4P

3. CONTACT RESISTANCE

: 30m Ω Max

4. INSULATION RESISTANCE

: DC 500V 100M Ω Min


5. WITHSTAND VOLTAGE

: AC 1500V 1 Minute

Rating:AC 10A 250V	
Mark	Safety Regulation
	VDE
	ENEC
	CCC
Rating:AC 15A 250V	
Mark	Safety Regulation
	cULus



富灣股份有限公司
 RICH BAY COMPANY LTD.
 台北縣樹林市東興街57號
 NO. 57, Tung Hsing St.,Shu-Lin Town,
 Taipei Hsien, Taiwan, R. O. C.
 TEL:886-2-86867781~4 FAX:886-2-86867780
 http://www.richbay.com.tw




DRAWN BY



UNIT UNIT Q'TY

APPROVED BY



TOLERANCE X.XX±0.1
 XX.XX±0.2
 XXX.XX±0.3

ID NO 221201A01
 DESCRIPTION

PRODUCT NO.

INTERIM NO.

NEW NO.

R-301SN(77) XX

REV

G