



- Robust aluminium housing including wire guard
- High flash power from two consecutive flashes
- High Protection rating IP 67
- Salt water resistant
- Robust bracket made of V2A stainless steel (accessory)

**TECHNICAL SPECIFICATIONS:**

Dimensions (Ø x Height):	153 mm x 198 mm
Housing:	Black laquered aluminium with integral wire guard
Lens:	PC, transparent
Fixing:	Base mounting
Connection:	Screw terminal with wire protection max. 2.5 mm ²
Cable entry:	Cable gland M20 x 1.5 mm (included in assembly) Cable diameter 6-13 mm
Installation position:	As required
Flash energy:	15 Ws
Flash frequency:	C. 1 Hz
Life duration:	4 x 10 ⁶ flashes

**ORDER SPECIFICATIONS:**

Voltage	24 V DC	230 V AC
Current consumption	800 mA	200 mA
red	839 152 55	839 152 68
yellow	839 352 55	839 352 68

**ACCESSORIES:**


Mounting bracket	975 839 02
------------------	-------------------

**TECHNICAL DIAGRAMS:**


see page 317



Generates a high signal effect thanks to two consecutive flashes

Sizes of Flashing Beacons

See note
on page 347



WERMA
SIGNALTECHNIK

