









建議剝線尺寸



SPECIFICATION:

1. Insulation Resistance: Over 100MΩ at 500V DC.
2. Dielectric strength: 2000V AC 1 Minute.
3. Body Material: Thermoplastic 94V-2~V-0.
4. The intended flexible cord:
 - a. Cord Size - 18AWG ~14AWG
 - b. Total Number of conductors-3 conductors
 - c. Overall cord diameter -8.0mm




Rating: AC 10A 250V	
Mark	Safety Regulation
	TUV
Rating: AC 15A 250V	
Mark	Safety Regulation
	CULUS



富灣(佛岡)五金電器有限公司

RICH BAY(FOGANG)HARDWARE ELECTRONIC CO.,LTD



DRAWN BY

UNIT

mm

UNIT QTY

1

SCALE

1:1

TOLERANCE

X.XX±0.1
XX.XX±0.2
XXX.XX±0.3

PRODUCT NO.

R-332(B202)

REV

ID NO

24032804Q

INTERIM NO.

DESCRIPTION

NEW NO.

D

李

2024.03.28

小英

APPROVED BY

朱

2024.03.28

显德