

OPTIGA™ Trust Charge

The trusted authentication solution for wireless charging

An increasing number of products and applications support wireless charging – driven by its obvious ease and convenience. However, an inaccurate power supply can be harmful to the device and, worst case scenario, even to the user.

Wireless charging authentication solution

Infineon's OPTIGA™ Trust Charge is a turnkey solution providing secured device authentication for inductive wireless charging according to the Qi2 wireless charging standard. Secured authentication with OPTIGA™ Trust Charge contributes to device and user safety by protecting against fake chargers.

The Qi2 wireless charging standard

Developed by the Wireless Power Consortium (WPC), the Qi standard defines wireless power transfer to small electronic devices with the aim of providing compatibility and safety for the device, and thus contributing to consumer safety. The Qi2 standard mandates the use of security-certified hardware to protect the authentication process.

It also mandates that keys and certificates be provisioned in a security-certified manufacturing environment. Chargers have to communicate with the device in question to prove their authenticity and compliance with the standard. Authentication of certified wireless chargers can prevent product damage as a result of unauthorized chargers and thereby can protect the consumer against safety hazards.

Enhanced security

The OPTIGA™ Trust Charge authentication chip is certified to Common Criteria EAL6+ (high), thus exceeding the security requirements of the Qi2 standard. Infineon is able to provide personalization and injection of the certificates and keys specified by the WPC in a secured and certified environment according to WPC requirements, making it easy for customers to build in security capabilities.

Fast and easy integration


The turnkey setup – with full system integration support and all key and certificate material preprogrammed – minimizes customer effort for design, integration and deployment. OPTIGA™ Trust Charge comes with preprogrammed locked OS, locked application code, and host-side modules to integrate with host microcontroller software. Integration support includes a reference board and documentation for rapid design-in.


Key features

- WPC Qi authentication (Qi2 and higher)
- Common Criteria EAL6+ (high) certified hardware
- ECDSA P-256 authentication
- NIST P-256, SHA-2 cryptography
- Up to 10 kB user memory
- Qi certificate format
- PKI
- I²C serial communication
- USON10-2 package (3 x 3 mm)
- Extended temperature range version available
- Full turnkey solution incl. drivers, SW library, preimplemented certificate(s) and key pair(s)

Applications

- Qi charging for mobile phones, tablets, laptops and other accessories





Benefits

- Protection of consumers against fake charging devices
- Turnkey solution with full system integration support including embedded software, host software, a development board, a reference board and documentation
- WPC-specific personalized keys and certificates pre-loaded at secured Infineon fabs
- Tiny package (3 x 3 mm) optimized for small devices
- Versions for standard and extended temperature ranges

The OPTIGA™ Trust family of products

OPTIGA™ Trust Charge is part of Infineon's OPTIGA™ Trust family, which offers a full range of embedded security solutions for the connected devices market.

Infineon's OPTIGA™ family is geared towards the protection of embedded systems. All OPTIGA™ products are based on secured hardware and software.

Product summary

Sales code	Temperature range [°C]	Package	SP number (for sample ordering)	Application area
SLS 32AIA020U2	-20 to +85	USON-10-2	SP005990599	Consumer electronics
SLS 32AIA020U3	-40 to +105	USON-10-2	SP005990601	Industrial applications

Published by
Infineon Technologies AG
Am Campeon 1-15, 85579 Neubiberg
Germany

© 2024 Infineon Technologies AG.
All rights reserved.

Public

Date: 05/2024

Please note!

This Document is for information purposes only and any information given herein shall in no event be regarded as a warranty, guarantee or description of any functionality, conditions and/or quality of our products or any suitability for a particular purpose. With regard to the technical specifications of our products, we kindly ask you to refer to the relevant product data sheets provided by us. Our customers and their technical departments are required to evaluate the suitability of our products for the intended application.

We reserve the right to change this document and/or the information given herein at any time.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life-endangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.



Scan QR code and explore offering
www.infineon.com