







DIM A.	(N-1)×10.0+5.9
DIM B	(N-1)×10.0

Δ_2 Dimension

Δ_2 N=Number of poles

POLES	DIM B	DIM A
2p-4p	± 0.15	± 0.20
5p-7p	± 0.20	± 0.25
8p-10p	± 0.25	± 0.30
11p-12p	± 0.30	± 0.40



PCB.LAYOUT
⚠ Bottom view

5		6		7	
SIGN	DATE	DESCRIPTION		APPROVER	
△	01/27/07	The soldering temperature from 24.5° to 250°		Aaron	
△	10/09/12	Update the drawing		Da cheng	
△	04/11/13	Update the drawing		Da cheng	
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!					

Material

- Item ① Terminal body (Contact pin): Brass, Tin plated
- Item ② Spring clamp: Stainless steel
- Item ③ Terminal Cover: Thermoplastic (UL94V-0)
- Item ④ Terminal Body: Thermoplastic (UL94V-0)
- Item ⑤ Pad board: Thermoplastic (UL94V-0)


Electrical

- Voltage rating: 300VAC
 - Current rating: 15A
 - Wire range:
 - Solid wire(AWG): 12-28
 - Stranded wire(AWG): 12-28
 - Pull force:
 - Screw:
 - Wire strip length: 5-6mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 260°C±5°C/5 Sec
 - Safety Approval:
- 

cULus

UL
- Critical dimension:

HG xx 10 x 0 xxxx G



ANYTEK										CUSTOMER COPY									
TITLE										HG 10.0mm Series									
PART NO.										HGxx10x00000G									
APPROVED										CHECKED		DESIGNED		DRAWN		DWG NO.		8HG04.01	
										CUST NO.									
														UNIT: mm		X.		±0.50	
														SCALE: NONE		X.X		±0.30	
																X.XX		±0.10	
										SHEET: 01/01		REV: F				X°		±1°	