ToughSonic®/PC Distance Sensor

Windows PC or Button Setup, Waterproof, Multiple Outputs

TSPC-30S1 Series

TSPC sensors and SenixVIEW software put the power of ultrasonics in your hands yet retain the simplicity of push-button TEACH setup. You can quickly adjust, optimize, save and clone your applications without calibration!

ToughSonic sensors contain a rugged transducer potted in a stainless steel housing for long life

Outputs respond to measured distance and non-contact technology means nothing touches your materials.

Many applications exist in all industries. Contact Senix today to discuss your specific needs.



Up to 14-ft. (4.3 m) maximum range in IP68 rated

Button TEACH or PC Configured Non-Contact Ultrasonic Distance Measurement

Features

Distance Measurements

- Long range, short dead band
- Unaffected by optical factors like color and transparency
- PC or button "teachable" setup
- Narrow beam with adjustments to optimize performance
- Temperature compensated

Packaging & Performance

- Ouick mounting
- Durable sealed housing for wet or dirty applications
- Short & overload protected I/O
- Multi-sensor synchronization
- · Adjustable sensitivity
- Rear status indicators (3)

Free Functionality


Use adjustable interface features like switch hysteresis and time delays to build complete solutions such as pump or material flow controllers. Save cost by eliminating PLCs, delay circuits and time delay relays!

PC Setup Power!

SenixVIEW PC

Software included!

Use SenixVIEW software (see separate data sheet) to select and adjust all interfaces, timing parameters, filters and modes. Then view, analyze or log data to optimize your application.



Several push-button "teach" features also provide common adjustments without the PC.

Stock, repairs, OEMs

Flexible configuration means fewer parts to stock and quick duplication! Higher volume OEM options are available.

Output Selection


In addition to the model's serial data interface there are two SenixVIEW selected outputs that can be analogs or switches to suit your application. All outputs have configurable features including ranges, target responses and time delays.


Voltage & Current Loop


Select voltage, current or both in standard (0-10 VDC, 4-20 mA) or custom ranges. The outputs are fully configurable and the analog slope can be positive or negative with distance.


Switches

One or two switches can be selected. Either or both can be "PNP" or "NPN" type (sourcing or sinking). Each has adjustable set point, hysteresis, window, initial conditions, ON delay, OFF delay and loss of target response for ultimate flexibility.













Senix® TSPC-30S1 ToughSonic® Distance Sensor

Specifications

Optimum Range	4 in 10 ft. (102 mm - 3 m)	Max Range	14 feet (4.3 meters)	
Case Material	316 stainless steel	Adjustment	Button "teach" or SenixVIEW	
Temperature	-40 to 158 F (-40 to 70 C)	Configuration	Stored in non-volatile memory	
Humidity	0 to 100% operating	Transducer	Ruggedized piezoelectric	
Compensation	Temperature compensated	Protection	NEMA-4X, NEMA-6P, IP68	
Resolution	Digital: 0.0034 in. (0.086 mm); An	alog:4099 steps (over full 0-10 VDC or 4-20 mA)	
Repeatability	Nominal 0.2% of range @ constant	nt temp. Affected I	by target, distance, environment	
Update Rate	20 Hz (50 ms), SenixVIEW adjustable; also affected by SenixVIEW filter selections			
Voltage Output	0-10, 0-5 VDC or PC customized,	10 mA max; Pusi	h-button teachable endpoints	
Current Loop	4-20 mA or PC customized, curre	nt sourcing, max.	loop 450Ω, teachable endpoints	
Sinking Switch	150 mA max. @ 40 VDC max., te	achable set point	& polarity, fault indication	
Sourcing Switch	150 mA max. @ input voltage, tea	achable set point &	& polarity, fault indication	
Output Select	Defaults are voltage & current loop; see Connections below for additional info			
RS-232, RS-485	Modbus protocol, 9600 to 115200 baud (selectable), 8 data bits, 1 stop, no parity			
SYNC feature	Permits up to 32 sensors to operate in close proximity without interaction			

Target Requirements

Objects		
Max. Distance		
Orientation		
Optical		

Detects flat or curved objects. Surface must reflect ultrasound back to sensor.

Affected by size, shape, orientation of target (sound level reflected back to sensor)

Flat surfaces should be oriented perpendicular to sensor output beam

Unaffected by target color, light, transparency or other optical characteristics

Connections

Cable Connection	Wire	Description		
Power	Brown	10-30 VDC @ 60 mA maximum; Typical: 45 mA @ 24 VDC (**)		
Ground	Blue	Power and interface common		
Voltage Output	White *	0-10 VDC, 0-5 VDC or custom end values between 0 and 10 VDC		
Current Loop Output	Black *	4-20 mA or user adjusted end values between 4 and 20 mA		
Switch #1 Output	Black *	Sinking ("NPN") or Sourcing ("PNP"), user selected		
Switch #2 Output	White *	Sinking ("NPN") or Sourcing ("PNP"), user selected		
RS-232 out / RS-485-	Gray	Serial data connection (depends on model - see part numbers)		
RS-232 in / RS-485+	Yellow	Serial data connection (depends on model - see part numbers)		
(*) Outputs on the block and white wires are Senix///EM colected. The block wire entires are 4.20 mA				

(*) Outputs on the black and white wires are SenixVIEW selected. The black wire options are 4-20 mA current loop or switch. White wire options are 0-10 VDC or switch. Switches can be sourcing or sinking. Max current loop resistance is derated below 15 VDC input voltage.


(**) At default update rate. Output currents not included. Sensitivity reduced below 15 VDC input voltage.

Part Numbers

Model Number	Description
TSPC-30S1-232	Serial RS-232 interface (PC COM port compatible)
TSPC-30S1-485	Serial RS-485 interface (allows addressable multi-sensor networks)

Senix also offers interconnection, communications, mounting, and display components

Dimensions



Mechanical

Dimensions are in inches (mm)

Mounting Hole: 1.2 in. (30.5 mm)

diameter

Standard Cable: 6.5ft (2m)

Ships with instructions and two 30mm stainless mounting nuts (other options available)

Total Weight: 10.40 oz. (0.29 kg)

Senix products are not recommended for applications with hazardous or explosive materials, or as a primary device for personal safety. Copyright 2008-2014, Senix® Corporation. All rights reserved. Printed in U.S.A.