





SMT / Solderable Standoff Nuts - M3 x 6mm - 10 pack

PRODUCT ID: 4206

These brilliant solder-able standoffs will make your mechanical PCB mounting problems go away. They're super simple – round M3 standoffs that are coated with tin so you can solder them in an oven or with a very powerful soldering iron & some patience. All you have to do is put a 4.25mm hole with 6.2mm solder ring on your PCB, then this components snout goes into the PCB, and solder it in place. The part is incredibly strong and saves you a hex nut or standoff. You don't even need a plated through hole (although it's recommend since they're stronger).


Fully threaded and works with any M3 machine screw

Need slightly shorter M3 standoffs? We also have a 10-pack of 3mm height!

TECHNICAL DETAILS

• 5.56mm diameter x 7.5mm total height (6mm above PCB, 1.5mm seated length)

• Diagram



METRIC	Thread Size x Pitch	Thru Hole +0.10 -0.08	Туре	Thread or Thru Hole Code	Length Code "L" ±0.13 (Length code in millimeters)						Min. Sheet Thickness	A Max.	C Max.	E ±0.13	ØH Hole Size In Sheet +0.08	ØD Min. Solder Pad
	M2 x 0.4	-	SMTS0	M2	2	3	4	6	8	10	1.53	1.53	2.6	5.56	3.73	6.2
	M2.5 x 0.45	_	SMTS0	M25	2	3	4	6	8	10	1.53	1.53	4.09	> 5.56	4.22	6.2
	M3 x 0.5	_	SMTS0	M3	2	3	4	6	8	10	1.53	1.53	4.09	5.56	4.22	6.2
	M3.5 x 0.6	_	SMTS0	M35	2	3	4	6	8	10	1.53	1.53	5.28	7:14	5,41	7.77
	M4 x 0.7	-	SMTS0	M4	2	3	4	6	8	10	1.53	1.53	6.22	8.74	6.35	9.37
	-	3.6	SMTS0	3.6	2	3	4	6	8	10	1.53	1.53	5.28	7.14	5.41	7.77
	-	4.2	SMTS0	4.2	2	3	4	6	8	10	1.53	1.53	6.22	8.74	6.35	9.37