

## **Product Description**

The Enterprise Grade DIY outdoor Gateway is an ideal product for IoT commercial deployment. It contains the Main Board, Operator-grade waterproof enclosure, backup battery and mounting accessories. The hardware main board completely integrates the WIFI, 4G, GPS and PoE main supply with an integrated back-up battery. The firmware implements a fully featured LoRaWAN™ complinant network base station. The Gateway has a range of over 15Km line-of-sight and over 2Km in dense urban environments.

The DIY Gateway brings more flexiblity for the developer to create an enterprise grade solution. Our most important difference is our flexible development support structure, allowing for faster development and time to market. We offer both a ready to go firmware image for openWRT based platforms and an open SDK for integration into hardware to support the needs of each customer. It can connect the standard NS (network server) and the local NS. And it also supports the built-in NS(By default, a license that supports 128 terminals and 5 external gateways is embedded). It does not need users to deploy NS in the cloud and locally, it saves the cost for server and R&D investment, and has the advantages of high execution efficiency and shorter delay.

# Package Content







Hardware Interfaces





## Feature Set

- Enterprise grade network gateway with your own configuration.
- LoRaWAN™ Stack Inside and integrate the Web UI for management.
- Complete Hardware specification including LoRa concentrator, Cellular, GPS and WIFI.
- Supports Power of Ethernet (PoE) IEEE 802.3af/at-Compliant Class 4, 48V.
- Battery Backup sustains operation for about 10 hours under typical conditions.
- IP67 waterproof enclosure with cable gland.



## Main Board

CPU:RAK634 Module(MT7628 inside)
RAM:128MB DDR2

RAM:128MB DDR Flash:16MB

WIFI: 2x2 MIMO 802.11b/g/n

LoRa concentrator

Standard version with 8 channel Gateway and also support Max.16 channel Gateway.

Tx Power is up to 27dBm and Rx sensitivity is down to -142dBm.

- 4G Cellular: Quectel EG95 for CAT4 cellular network
- L70 GPS Module
- Power-over-Ethernet (PoE): 100M base-T Ethernet with IEEE802.3af/at standard PoE.

## Accessories

- Mounting Kit
- PoE Injector
- Antennas (WiFI Antenna, GPS Antenna, LoRa Antenna, LTE Antenna)

## **Enclosure**

- IP67 waterproof white color.
- Interface: 5 x N-Type connectors for Antenna,1 PoE port and 1 reserve port.
- Weight (with cable): approximately 70.54oz (2kg).
- Dimensions: 220mm x 220mm x 104mm.
- Wall thickness: 2mm.
- Support up to 70~100 mm diameter pole mount

## **Backup Battery**

- The maximum space in the Enclosure can be placed 12V/10AH batteries for about 10 hours lifetime under typical operation.
- Battery powered real time clock.
- Battery Within 140 x 70 x 30mm.
- DC 5.5 x 2.1 circular joint with two interfaces, one male and one female.

# Supported Software

#### For LoRa

- Supports class A , C
- Supports LoRaWAN protocol
- Country code setup
- TX power setup
- Data logger
- Statistic
- Location setup
- Server address & port setup

#### For Network

- WiFi AP mode
- LTE APN setup
- Uplink backup
- Supports 802.1q
- DHCP Server/Client
- Router module NAT
- Firewall

## For Management

- WEB Management
- Supports SSH2, NTP
- Firmware update
- Supports configure the LoRa Packet Forwarder
- Supports Build-in LoRa Server
- Supports OpenVPN, Ping Watch Dog
- Supports MQTT Bridge

# **DIY Configuration**

Part Number	8 Channel SX1301	16 channel SX1301	Cat4 Cellular	GPS	WIFI	Battery Backup
RAK7249-0x-14x	√		√	√	√	
RAK7249-1x-14x		√	√	√	√	
RAK7249-2x-14x	√		√	√	√	V
RAK7249-3x-14x		√	√	√	√	V
RAK7249-0x	√			√	√	
RAK7249-1x		√		√	√	
RAK7249-2x	√			√	√	<b>V</b>
RAK7249-3x		√		√	√	√



# **Key Features**

Computing	<ul> <li>MT7628, DDR2RAM 128MB</li> </ul>
WIFI Feature	<ul> <li>Frequency: 2.400 - 2.4835GHz</li> <li>(802.11b/g/n)</li> <li>RX Sensitivity: -95dBm (Min)</li> <li>TX Power: 20dBm (Max)</li> </ul>
LoRa Feature	<ul> <li>SX1301 Mini PCle card</li> <li>8 Channels (Optional: 16 channels)</li> <li>TX Power: 27dBm (Max)</li> <li>RX Sensitivity: -142dBm (Min)</li> </ul>
Cellular	Supports Quectel EG95-E / EG95-NA(IoT/M2M-optimized LTE Cat 4 Module)     EG95-E for EMEA Region LTE FDD: B1/B3/B7/B8/B20/B28A WCDMA: B1/B8 GSM/EDGE: B3/B8     EG95-NA for North America Region LTE FDD: B2/B4/B5/B12/B13 WCDMA: B2/B4/B5
Power Supply	<ul> <li>POE (IEEE 802.3af), 42~57VDC</li> </ul>
Power Consumption	• 12W (typical)
ETH	• RJ45 (10/100M)
Antenna	<ul> <li>5 N-Type connectors</li> </ul>
Ingress Protection	• IP67
Enclosure Material	Aluminum
Weight	<ul> <li>Approximately 111.11oz (3.15kg with mounting kit)</li> </ul>
Dimension	• 220mm x 220mm x 104mm
Operating Temp.	• -30°C ~ +55°C
Installation Method	<ul> <li>Pole or Wall mounting</li> </ul>

# **RF Specifications**

Wireless Standard	• IEEE 802.11b/g/n
Wi-Fi Operating Frequency	• ISM band: 2.412~2.472(GHz)
Wi-Fi Operation Channels	• 2.4GHz: 1-13
Wi-Fi Transmit Power  (The maximum power may be different depending on local regulations)	<ul> <li>802.11b</li></ul>
Wi-Fi Receiver Sensitivity (Typical)	<ul> <li>802.11b         <ul> <li>95dBm@ 1Mbps</li> </ul> </li> <li>802.11g         <ul> <li>90dBm @6 Mbps</li> <li>75dBm@54Mbps</li> </ul> </li> <li>802.11n(2.4G)         <ul> <li>89dBm@MCS0 (HT20)</li> <li>72dBm @MCS7(HT20)</li> <li>86dBm @MCS0(HT40)</li> <li>68dBm @MCS7(HT40)</li> </ul> </li> </ul>
LoRa Operating Frequency	• EU433 / CN470 / EU868 / US915 / AU915 / AS923 / AS920 / KR920 / IN865
LoRa TX Power	• 27 dBm (Max)
LoRa RX Sensitivity	• -142 dBm (Min)
Compliance	• CE, FCC, RCM

## **Order Information**

Part Number	Description
RAK7249-03-142	8 channel DIY Gateway with Cat 4 Cellular + GPS for EU868 region
RAK7249-04-141	8 channel DIY Gateway with Cat 4 Cellular + GPS for US915 region
RAK7249-13-142	Advanced version, 16 channel DIY Gateway with Cat 4 Cellular + GPS for EU868 region
RAK7249-14-141	Advanced version, 16 channel DIY Gateway with Cat 4 Cellular + GPS for US915 region



# About RAKwireless:

RAKwireless is the pioneer in providing innovative and diverse cellular and LoRaconnectivity solutions for IoT edge devices. It's easy and modular design can be used in different IoT applications and accelerate time-to-market. For more information, please visit Rakwireless website at www.rakwireless.com.