


RECOMMENDED
HOLE PATTERN



RoHS Compliant

MATERIALS

BODY	BRASS
BODY PLATING	GOLD
CONTACT	BERYLLIUM COPPER
CONTACT PLATING	GOLD
DIELECTRIC	TEFLON (PTFE)

50 Ohm IMPEDANCE
500V PEAK VOLTAGE RATING
TEMPERATURE RANGE: -55°C TO +155°C
INTERFACE DIMENSIONS SIMILAR TO MIL-C-39012

MILLIMETER WAVE TECHNOLOGIES
6501 W. FRYE ROAD, #23
CHANDLER, AZ 85226

SMA FEMALE JACK
RIGHT ANGLE PCB MOUNT

Designed by P. CHEN	Checked by S. NEUGESS	Approved by A. LEE	File name MWA-3300-G-B	TITLE MWA-3300-G-B
TOLERANCES DIMENSIONS IN INCHES UNLESS OTHERWISE SPECIFIED DECIMALS .XX ± .02 .XXX ± .005				REV. 4 DATE 051509
ALL DIMENSIONS ON THIS DRAWING ARE FOR REFERENCE PURPOSES ONLY AND ARE SUBJECT TO CHANGE.				Scale NONE Sheet 1 of 1

RevNo	Revision Notes	Date	Checked
1	Initial Release	051509	PC
2	Stand-off pads added; Contact diameter changed	021314	GC
3	Center pin to end of threads dimension revised	021914	GC
4	Body changed to 6.3mm square	051514	GC