

Conductor marker - UC-WMCO 2,1 (12X3) - 0827120

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Conductor marker, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: slide on, Cable diameter: 1.6-2.1 mm, Lettering field: 12 x 3 mm



Why buy this product

- The UC-WMCO ... UniCard labeling range includes thread-on markers for the subsequent labeling of conductors by simply sliding them on using the UC-WMCO ... TOOL
- Large-surface labeling option in a space-saving design
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- Secure tight fit even in the event of vibrations
- The format automatically ensures printing with a high degree of positioning accuracy
- The sheets provide space for including function texts



Key Commercial Data

Packing unit	10 STK
Minimum order quantity	10 STK
GTIN	 4 046356 440226
GTIN	4046356440226
Weight per Piece (excluding packing)	8.850 g
Custom tariff number	39269097

Technical data

Dimensions

Width (a)	12 mm
Cable diameter	1.6 mm ... 2.1 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Conductor marker - UC-WMCO 2,1 (12X3) - 0827120

Technical data

General

Color	white
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	40
Number of individual labels per row	10
Printability	UV LED technology
Device	5147999 BLUEMARK CLED
	5144615 CMS-P1-PLOTTER
	5146568 P1 UC-MAG 7
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	slide on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
----------	----------

Conductor marker - UC-WMCO 2,1 (12X3) - 0827120

Classifications

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001530
ETIM 6.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410

Accessories

Accessories

Assembly tool

Alignment tool for cable markers - UC-WMCO 2,1 TOOL - 0827803



Alignment tool for cable markers, orange, Mounting type: slide on, Cable diameter: 1.6-2.1 mm

Alignment tool for cable markers - UC-WMCO TOOL SET - 0827807



Alignment tool for cable markers, orange, unlabeled, Mounting type: slide on, Cable diameter: 1.6-7 mm

Magazine

Magazine - P1 UC-MAG 7 - 5146568

Magazine, for CMS-P1-PLOTTER, for accommodating: UC-WMCO...

