





RevNo	Revision note	Date	Checked
1	Initial Release	060606	GC



NOTES:

- STRIP CABLE ENDS IN ACCORDANCE WITH CONNECTOR SPEC SHEETS.
- CONSTRUCT CABLE ASSEMBLY IN ACCORDANCE WITH PROCEDURES.
- TAG WITH PART NUMBER, QUANTITY, AND CUSTOMER PART NUMBER.
- ALL COMPONENTS MUST BE ROHS COMPLIANT

PART NO.	DIM "A"	
	INCHES	MILLIMETERS
MWAS-1710-6.00	6.00	152.40
MWAS-1710-10.00	10.00	254.00
MWAS-1710-12.00	12.00	304.80
MWAS-1710-18.00	18.00	457.20
MWAS-1710-24.00	24.00	609.60
MWAS-1710-31.00	31.00	787.40
MWAS-1710-36.00	36.00	914.40
MWAS-1710-1M	39.37	1000.00
MWAS-1710-48.00	48.00	1219.20
MWAS-1710-60.00	60.00	1524.00
MWAS-1710-72.00	72.00	1828.80
MWAS-1710-2M	78.74	2000.00

MATERIALS

- COAXIAL CABLE, HARBOUR SS402
- MWA-6010AS-141 SMA PLUG for RG402
- SHRINK TUBING, 5/16" BLACK POLYOLEFIN

MILLIMETER WAVE TECHNOLOGIES
6501 W. FRYE ROAD, #23
CHANDLER, AZ 85226

CABLE ASSEMBLY
SMA PLUG to SMA PLUG
SS402

Designed by N. JAIN	Checked by W. CANON	Approved by N. JAIN	File name MWAS-1710	TITLE MWAS-1710	
TOLERANCES DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED DECIMALS ANGULAR .XX ± .02 ± .06 .XXX ± .005 DO NOT SCALE THIS DRAWING		ALL DIMENSIONS ON THIS DRAWING ARE FOR REFERENCE PURPOSES ONLY AND ARE SUBJECT TO CHANGE		REV. 1	Scale NONE
				DATE 120503	Sheet 1 of 1