

SPECIFIED

.XX

±0.25

±0.15


DO NOT MAKE MANUAL REVISIONS TO MASTER. UNLESS OTHERWISE SPECIFIED, ALL RADIUS ARE 0.2 MM



ORIGINAL


ISSUE NUMBER


(1)



LCP +30% GLASS REINFORCED. UL94V-0 PHOSPHOR BRONZE PHOSPHOR BRONZE GOLD FLASH PLATING ON CONTACT AREA MATTE TIN PLATING 30~100µ" ON SOLDER

TAIL OVER NICKEL 50~150µ" UNDER PLATING





PCB HOLE DIM: DRILLED HOLE =  $0.550\pm0.020$ mm FINISHED HOLE = 0.460±0.050mm Cu THICKNESS = 0.0375±0.0125mm Au THICKNESS = 0.007±0.003mm Ni THICKNESS = 0.0044±0.0032mm OR Ag THICKNESS = 0.0003±0.002mm

ACAD REFERENCE NO.:

PART NUMBER:

## ZD+ CONNECTOR, MALE, VERTICAL, 4 PAIR



**EDAC INC** TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DATE: JUNE.27 /2018 DRAWN: CHECKED: DATE: SCALE: N.T.S SHEET 1 OF DRAWING NUMBER: 500-080-231-H01 ISSUE

500-080-231-H01

500-080-231-H01

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.