
# **Technical Data Sheet**

# Rosenberger

Insert Mini-Coax 6 Channel Block Right Angle

23C25G-40ML5



All dimensions are in mm; tolerances according to ISO 2768 m-H

# Interface

According to

Rosenberger Mini-Coax

# **Documents**

PCB - Layout

B 501B

# Material and plating Connector parts

Center contact Outer contact male Outer contact female

Body Dielectric

# Material **Plating**

CuBe or equiv. AuroDur®, gold plated AuroDur®, gold plated AuroDur®, gold plated CuBe Brass **Brass** AuroDur®, gold plated

**PTFE** 

Tel. : +49 8684 18-0 Email: info@rosenberger.de Page

1/2

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

# Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

# RF\_35/08.13/6.1

# Technical Data Sheet Rosenberger Insert Mini-Coax Right Angle Rosenberger 23C25G-40ML5

# **Electrical data**

Impedance 50  $\Omega$ 

Frequency DC to 40 GHz

Return loss  $\geq$  25 dB @ DC to 3 GHz  $\geq$  20 dB @ 3 GHz to 6 GHz  $\geq$  16 dB @ 6 GHz to 20 GHz

≥ 12 dB @ 20 GHz to 40 GHz

Insertion loss  $\leq 0.04 \text{ x } \sqrt{f} \text{ [GHz] dB}$ 

 $\begin{array}{ll} \mbox{Insulation resistance} & \geq 1 \mbox{G} \Omega \\ \mbox{Center contact resistance} & \leq 10 \mbox{ m} \Omega \\ \mbox{Outer contact resistance} & \leq 3 \mbox{ m} \Omega \\ \mbox{Test voltage (at sea level)} & 750 \mbox{ V rms} \\ \mbox{Working voltage (at sea level)} & 500 \mbox{ V rms} \end{array}$ 

RF-leakage  $\geq$  80 dB @ DC to 1 GHz  $\geq$  60 dB @ 1 GHz to 4 GHz

- Connector only, VSWR in application depends decisive on PCB layout -

# Mechanical data

Mating cycles ≥ 500

Engagement force max. 40 N typical 30 N Extraction force max. 45 N typical 30 N

# **Environmental data**

Temperature range -40 °C to +125 °C Climatic category IEC 60068-2-1 40/85/21 Dry heat IEC 60068-2-2 Damp heat IEC 60068-2-78

Shock IEC 60068-2-27 (50g halfsinus, 2 shocks/axis during 11 sec.)

Max. soldering temperature IEC 61760-1, +260 °C for 10 sec.

RoHS compliant

**Tooling** 

N/A

Weight

3 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

	Draft	Date	Approved	Date	Rev.	Engineering (
	Martin Moder	22.11.16	Herbert Babinger	15.03.18	200	17-
ı						

Tel. : +49 8684 18-0 Email : info@rosenberger.de

change number

-2028

Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de Page

Date

12.03.18

Name

Andreas Plötz

2/2