

### 3M™ Star Mandrel

Part Number 944, 3M ID 61500059946, UPC 00048011139289



# **Specifications**

<b>Attachment</b>	Type	Threaded

Brand 3M™

Converted Form Mandrel, Mandrel/Spindle

**Equipment -**

Machines Die Grinders

Form Type Star

Industries Metalworking

Length 3 Inch Length (Metric) 76.2 mm Max RPM 24100

**Overall Length** 

(metric) 76.2 mm

Product Form Mandrel

Shank Size 0.25 Inch

**Shank Size** 

(metric) 6.35 mm

Builders Hardware, Medical Instruments, Metal Fabrication, Metal Implants,

Sub Industries Plating & Polishing, Plumbing Fixtures, Turbine Engines

Thread Size 1/4-20 EXT

Type Regular

## **Product Details**

- Securely attaches Scotch-Brite<sup>™</sup> Stars to die grinder
- Enables die grinder to reach internal diameters of pipes, tubing
- Shank size is 0.25 inches
- Thread size is 1/4-20 EXT
- Runs at maximum RPM of 24,100

Our 3M<sup>™</sup> Star Mandrel enables you to tightly secure Scotch-Brite<sup>™</sup> Stars with 1/4-20 internal threads to your die grinder for safe performance. This accessory allows you to deburr inside diameters of pipe and tubing.



Unique shape for cleaning, polishing and light deburring of inside diameters of pipe and tubing

#### Get More Done with One Tool

With our <u>3M™ Star Mandrel</u> (PDF, 2.9 Mb), you can use your die grinder with our uniquely shaped Scotch-Brite™ Stars to clean, polish and lightly deburr the inside diameters of pipe and tubing. Our 3M™ Star Mandrel is 3 inches in length with a shank size of .0.25 inches. Thread size is 1/4-20 EXT. It will run safely at a maximum RPM of 24,100.

#### Maximize the Value of Your 3M™ Power Tools

Engineered to work effectively with your 3M<sup>™</sup> Die Grinder, our 3M<sup>™</sup> Star Mandrel allows you to do more, more cost-efficiently with your power tools.