

RAMO 22 S, M12, round collar, 1 NO, Gold, M12 4-pin A-coded, frontring black, 1 x 90°, shape V, latching



fields of application

- > Measurement-control-regulation
- > Electrical engineering
- > Mechanical and system engineering
- > Signalling systems
- > Vehicle construction
- > Chemical industry
- > Industrial robots

special features

- > Precise haptics
- > Safe gold contacts
- > Simple M12 plug&play connection
- > Protected contacts due to sealed housing

CE

NEW

description

Selector switch with various switching positions and M12 terminal

technical data

> general		
illuminated	Yes	direct links
Color	black	> RAFI eCatalog
Bezel color	white	
Collar color	black	
Front ring color	black	
Luminous element color	white	
Collar shape	round	
Operating temperature, min.	-25 °C	
Operating temperature, max.	70 °C	
Storage temperature, min.	-40 °C	
Storage temperature, max.	90 °C	
Luminous elements	LED	
Shock resistance according to	30 g at 11 ms amplitude semi-sinusoidal	
standard IEC 60068-2-27		
Packaging	Box	
Packaging unit	2 pcs.	
Environment resistance	IEC 60068-2-14	
	IEC 60068-2-30	
	IEC 60068-2-78	
Operating life	200,000 Cycles	
B10	250,000 Cycles	
Degree of protection, front side, according to DIN EN 60529	IP65	

The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which my change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights. **date**: Aug 16, 2019 **page**: 1/3

RAFI GmbH & Co. KG

Ravensburger Str. 128-134 88276 Berg / Ravensburg Germany www.rafi.de, info@rafi.de technical data sheet

1.10.021.204/0221



	Degree of protection, rear side,	IP65
	according to DIN EN 60529	11 00
	Salt-spray resistance according to	IEC 60068-2-11
	standard	
	RoHS compliant	Yes
	REACH compliant	Yes
	Potential free	yes
	oscillation restistance according to standard IEC 60068-2-6	5 g at 10500 Hz
>	mounting diameters	
	Mounting hole	22.3 mm
	Mounting depth	30.05 mm
	Installation height	23.83 mm
	Outside dimension, length	29.8 mm
	Outside dimension, width	29.8 mm
	Outside dimension, height	53.88 mm
>	mechanical data	
	Actuation function	latching
	Contact function	1 NO
	Contact material	Gold
	Rotating angle	1 x 90°, shape V
	Fixing	Threaded ring
	Terminal on the rear	M12 4-pin A-coded
	PIN 1	Normally open contact 1
	PIN 2	LED +
	PIN 3	GND
	PIN 4	Normally open contact 1
>	electrical data	
	Operating voltage of the luminous element, min.	22 V
	Operating voltage of the luminous element, max.	26 V
	Operating current of the luminous element, max.	25 mA
	Rated voltage, min.	10 V
	Rated voltage, max.	32 V
	Rated current, max.	0.1 A

RAFI GmbH & Co. KG


Ravensburger Str. 128-134 88276 Berg / Ravensburg Germany www.rafi.de, info@rafi.de technical data sheet

1.10.021.204/0221




drawings


Dimensioned drawing




Mounting hole drawing



Dimensioned drawing



Schematic diagram



The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which my change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights. **date**: Aug 16, 2019 **page**: 3/3

RAFI GmbH & Co. KG

Ravensburger Str. 128-134 88276 Berg / Ravensburg Germany www.rafi.de, info@rafi.de