

# APPROVAL SHEET

RFBPF Series – 1608(0603)- RoHS Compliance

**MULTILAYER CERAMIC BAND PASS FILTER** 

**Halogens Free Product** 

5GHz ISM Band RF Application

P/N: RFBPF1606K16T

\*Contents in this sheet are subject to change without prior notice.

## **FEATURES**


- 1. Miniature footprint: 1.6 X 0.8X 0.6 mm<sup>3</sup>.
- 2. Low Insertion loss
- 3. High attenuation on harmonic suppressed
- 4. LTCC process

## **APPLICATIONS**

1. 4900 ~ 6425 MHz working frequency.

## CONSTRUCTION

Top view



| PIN | Connection  |  |
|-----|-------------|--|
| 1   | Input port  |  |
| 2   | GND         |  |
| 3   | Output port |  |

## **DIMENSIONS**


| Figure  | Symbol | Dimension (mm) |
|---|--------|----------------|
|   | L      | 1.60 ± 0.10    |
| L   | W      | 0.80 ± 0.10    |
| Top view W Side view  Bottom view B A B A B A B | Т      | 0.60 ± 0.10.   |
|   | А      | 0.55 ± 0.10    |
|   | В      | 0.60 ± 0.10    |
|   | С      | 0.25 ± 0.10    |
|   | D      | 0.23 ± 0.10    |
|   | E      | 0.40 ± 0.10    |
|   | F      | 0.12 ± 0.10    |
|   | G      | 0.125 ± 0.10   |



## **ELECTRICAL CHARACTERISTICS**

| RFBPF1606K16T  | Specification  |  |
|--|--|--|
| Francisco Pagas  | 4900 ~ 5950 MHz  |  |
| Frequency Range  | 5950 ~ 6425 MHz  |  |
| Inspertion Lang (at 25 °C)   | 1.0 dB max. @4900 ~ 5950 MHz   |  |
| Insertion Loss (at 25 °C)  | 1.6 dB max. @5950 ~ 6425 MHz   |  |
| Insertion Loss (at -40 ~ +85 °C)   | 1.2 dB max. @4900 ~ 5950 MHz   |  |
| insertion coss (at -40 = +65 C)  | 1.8 dB max. @5950 ~ 6425 MHz   |  |
|  | 38.0 dB min. @ 30 ~ 2700 MHz   |  |
|  | 35.0 dB min. @ 3400 ~ 3800 MHz   |  |
| Attenuation  | 15.0 dB min. @ 6900 MHz  |  |
|  | 20.0 dB min. @ 7250 ~ 7800 MHz   |  |
|  | 20.0 dB min. @ 10300 ~ 11700 MHz   |  |
| Return Loss  | 10 dB min.   |  |
| Impedance  | 50 Ω   |  |
| Operating Temperature Range  | -40 ~ +85°C  |  |
| Power capacity   | 500mW  |  |
| Moisture sensitivity levels  | MSL is LEVEL 1 (Refer to : IPC/JEDEC J-STD-020)                                    |  |
| Typical El   | ectrical Chart   |  |
| 25 -10 -15 -20 -25 -30 -35 -50 -55 -60 | -Return Loss<br>-Insertion Loss<br>5.5 6.5 7.5 8.5 9.5 10.5 11.5 12.5<br>freq, GHz |  |

# LAND PATTERN





# **RELIABILITY TEST**

| Test item                    | Test condition / Test method  | Specification  |
|------------------------------|---|--|
| Solderability                | *Solder bath temperature : 235 $\pm$ 5°C                                    | At least 95% of a surface of each terminal           |
| JIS C 0050-4.6               | *Immersion time: 2 ± 0.5 sec  | electrode must be covered by fresh solder.           |
| JESD22-B102D                 | Solder : Sn3Ag0.5Cu for lead-free   |  |
| Resistance to soldering heat | *Preheating temperature: 120~150°C,   | No mechanical damage.                                |
| JIS C 0050-5.4               | 1 minute.   | Electrical specification shall satisfy the           |
|                              | *Solder temperature: 270±5°C  | descriptions in electrical characteristics under     |
|                              | *Immersion time: 10±1 sec   | the operational temperature range within -40         |
|                              | Solder : Sn3Ag0.5Cu for lead-free   | ~ 85°C.  |
|                              | Measurement to be made after keeping at                                     | Loss of metallization on the edges of each           |
|                              | room temperature for 24±2 hrs   | electrode shall not exceed 25%.                      |
| Drop Test                    | *Height: 75 cm  | No mechanical damage.                                |
| JIS C 0044                   |   | Electrical specification shall satisfy the           |
| Customer's specification.    | *Test Surface : Rigid surface of concrete or steel.                         | descriptions in electrical characteristics under     |
|                              | *Times : 6 surfaces for each units ; 2 times for each side.                 | the operational temperature range within -40 ~ 85°C. |
|                              | for each side.  |  |
| Vibration                    | *Frequency: 10Hz~55Hz~10Hz(1min)  | No mechanical damage.                                |
| JIS C 0040                   | *Total amplitude: 1.5mm   | Electrical specification shall satisfy the           |
|                              | ·   | descriptions in electrical characteristics under     |
|                              | *Test times: 6hrs.(Two hrs each in three mutually perpendicular directions) | the operational temperature range within -40         |
|                              | mutually perpendicular directions)  | ~ 85°C.  |
| Adhesive Strength            | *Pressurizing force :   | No remarkable damage or removal of the               |
| of Termination               | 5N(≦0603) ; 10N(>0603)  | termination.   |
| JIS C 0051- 7.4.3            | *Test time: 10±1 sec  |  |
| Bending test                 | The middle part of substrate shall be                                       | No mechanical damage.                                |
| JIS C 0051- 7.4.1            | pressurized by means of the pressurizing rod                                | Electrical specification shall satisfy the           |
|                              | at a rate of about 1 mm/s per second until the                              | descriptions in electrical characteristics under     |
|                              | deflection becomes 1mm/s and then pressure                                  | the operational temperature range within -40         |
|                              | shall be maintained for 5±1 sec.  | ~ 85°C.  |
|                              | Measurement to be made after keeping at                                     |  |
|                              | room temperature for 24±2 hours   |  |

| Approvai sneet   |  |  |
|--|--|--|
| Temperature cycle JIS C 0025   | <ol> <li>30±3 minutes at -40°C±3°C,</li> <li>10~15 minutes at room temperature,</li> <li>30±3 minutes at +85°C±3°C,</li> <li>10~15 minutes at room temperature,</li> <li>Total 100 continuous cycles</li> <li>Measurement to be made after keeping at room temperature for 24±2 hrs</li> </ol>                           | No mechanical damage.  Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.  |
| High temperature  JIS C 0021  Humidity (steady conditions)  JIS C 0022 | *Temperature: 85°C±2°C  *Test duration: 1000+24/-0 hours  Measurement to be made after keeping at room temperature for 24±2 hrs  *Humidity: 90% to 95% R.H.  *Temperature: 40±2°C  *Time: 1000+24/-0 hrs.  Measurement to be made after keeping at room temperature for 24±2 hrs  % 500hrs measuring the first data then | No mechanical damage.  Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.  No mechanical damage.  Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C. |
| Low temperature JIS C 0020   | *Temperature : -40°C±2°C  *Test duration : 1000+24/-0 hours  Measurement to be made after keeping at room temperature for 24±2 hrs   | No mechanical damage.  Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.  |



# **SOLDERING CONDITION**

Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2,





Fig 2. Infrared soldering profile

## **ORDERING CODE**

| RF        | BPF              | 1606                    | K           | 16           | Т          |
|-----------|------------------|-------------------------|-------------|--------------|------------|
| Walsin    | Product Code     | Dimension code          | Application | Specificatio | Packing    |
| RF device | BPF:             | Per 2 digits of Length, | K:5GHzISM   | n            | T : Reeled |
|           | Band Pass Filter | Width, Thickness:       | Band        | Design code  |            |
|           |                  | e.g. :                  |             |              |            |
|           |                  | 160806 =                |             |              |            |
|           |                  | Length 16,              |             |              |            |
|           |                  | Width 08,               |             |              |            |
|           |                  | Thickness06             |             |              |            |

Minimum Ordering Quantity: 4000 pcs per reel.


## **PACKAGING**



# Paper Tape specifications (unit :mm)

| Index          | Ao          | Во            | ΦD              | Т             | W               |
|----------------|-------------|---------------|-----------------|---------------|-----------------|
| Dimension (mm) | 0.975± 0.10 | 1.76 ±0.10    | 1.55 + 0.05     | 0.75± 0.10    | 8.0 ± 0.10      |
| Index          | E           | F             | Po              | P1            | P2              |
| Dimension (mm) | 1.75 ± 0.10 | $3.50\pm0.05$ | $4.00 \pm 0.10$ | $4.00\pm0.10$ | $2.00 \pm 0.05$ |

#### **Reel dimensions**



| Index          | Α      | В     | С     |
|----------------|--------|-------|-------|
| Dimension (mm) | Ф178.0 | Ф60.0 | Ф13.0 |

Taping Quantity:4000 pieces per 7" reel

#### **CAUTION OF HANDLING**

### **Limitation of Applications**

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects, which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Medical equipment
- (5) Disaster prevention / crime prevention equipment
- (6) Traffic signal equipment
- (7) Transportation equipment (vehicles, trains, ships, etc.)
- (8) Applications of similar complexity and /or reliability requirements to the applications listed in the above.

#### Storage condition

- (1) Products should be used in 6 months from the day of WALSIN outgoing inspection.
- (2) Storage environment condition.
  - Products should be storage in the warehouse on the following conditions.

■ Temperature : +5 to +40°C

Humidity : 30 to 70% relative humidity

- Don't keep products in corrosive gases such as sulfur. Chlorine gas or acid or it may cause oxidization of electrode, resulting in poor solderability.
- Products should be storage on the palette for the prevention of the influence from humidity, dust and son on.
- Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
- Products should be storage under the airtight packaged condition.