



## INDUSTRIAL/MACHINE VISION APPLICATIONS

# FLIR BLACKFLY<sup>®</sup> S

P/N BFS-PGE-120S4

### SMALL PACKAGE, POWERFUL RESULTS

The Blackfly S is a compact, high performance machine vision camera that allows designers to easily produce the exact images they need. With both automatic and precise manual control over image capture and on-camera pre-processing, the Blackfly S accelerates application development.

[www.flir.com/mv](http://www.flir.com/mv)

### FEATURES

#### THE LATEST CMOS SENSORS

Switch between high sensitivity and low noise, and high saturation capacity and dynamic range with selectable conversion gain.

#### IMPROVE CYCLE TIMES

Automate more with advanced camera controls, event notifications, chunk data, counters and timers.

#### ACCELERATE YOUR TIME TO MARKET

FLIR's GenICam3 API with GUI library, and detailed event logging is supported by comprehensive documentation.

### APPLICATIONS

AUTOMATED OPTICAL INSPECTION

MICROSCOPY

ROBOT GUIDANCE

LASER BEAM PROFILING

AUTONOMOUS VEHICLE GUIDANCE



GEN*<i>*CAM

Pregius

SPECS	BFS-PGE-120S4M-CS	BFS-PGE-120S4C-CS
Resolution	4000 x 3000	
Frame Rate*	10 FPS / 26 FPS with Lossless Compression	
Megapixels	12 MP	
Chroma	Mono	Color
Sensor	Sony IMX226, CMOS, 1/1.7"	
Readout Method	Rolling shutter with global reset	
Pixel Size	1.85 $\mu$ m	
Lens Mount	CS-mount	
ADC	10-bit / 12-bit	
Minimum Frame Rate**	1 FPS	
Gain Range**	0 to 47 dB	
Exposure Range**	15 $\mu$ s to 30 s	
Acquisition Modes	Continuous, Single Frame, Multi Frame	
Partial Image Modes	Pixel binning, decimation, ROI	
Image Processing	Gamma, lookup table, and sharpness	Color correction matrix, gamma, lookup table, saturation, and sharpness
Sequencer	Up to 8 sets using 5 features	
Image Buffer	240 MB	
User Sets	2 user configuration sets for custom camera settings	
Flash Memory	6 MB non-volatile memory	
Opto-isolated I/O	1 input, 1 output	
Non-isolated I/O	1 bi-directional, 1 input	
Auxiliary Output	3.3 V, 120 mA maximum	
Interface	GigE PoE	
Power Requirements	Power over Ethernet (PoE), or 12 V nominal (8 - 24 V) via GPIO	
Power Consumption	3 W maximum (2.8 W nominal)	
Dimensions/Mass	29 mm x 29 mm x 30 mm / 36 g	
Machine Vision Standard	Gige Vision v1.2	
Compliance	CE, FCC, KCC, RoHS, REACH. The ECCN for this product is: EAR099.	
Temperature	Operating: 0°C to 50°C Storage: -30°C to 60°C	
Humidity	Operating: 20% to 80% (no condensation) Storage: 30% to 95% (no condensation)	
Warranty	3 years	

\*Frame rates are measured with Device Link Throughput Limit of 125 MBps and Acquisition Frame Rate disabled.

\*\*Values are the same in binning and no binning modes.



#### FLIR Integrated Imaging Solutions

##### CANADA

12051 Riverside Way  
Richmond, BC, Canada  
V6W 1K7  
T: +1 866.765.0827 (toll free)  
T: +1 604.242.9937  
F: +1 604.242.9938  
E: mv-sales@flir.com  
www.flir.com/mv

##### USA

T: +1 866.765.0827 (toll free)  
E: mv-na-sales@flir.com

##### EUROPE

T: +49 7141 488817-0  
F: +49 7141 488817-99  
E: mv-eusales@flir.com

##### CHINA

T: +86 10 8215 9938  
F: +86 10 8215 9936  
E: mv-chinasales@flir.com

##### ASIA

E: mv-asiasales@flir.com

www.flir.com  
NASDAQ: FLIR

©2019 FLIR® Integrated Imaging Solutions Inc. All rights reserved.  
Names and marks appearing on the products herein are either registered trademarks or trademarks of FLIR® Systems, Inc. and/or its subsidiaries. Specifications are subject to change without notice.

VN: BFS-PGE-120S4-v2

FIND THE BEST BLACKFLY S FOR YOUR NEEDS



The World's Sixth Sense®