



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
01		2020/02/21	Jane	New Initial



M SAP - XX P M M S - S F 8 001

SAP: A-Code Plastic

03: 3Pin

04: 4Pin

05: 5Pin

06: 6Pin

08: 8Pin

10: 10Pin

12: 12Pin

P: Panel (板端)

M: Male Connector (公座)

001: PG9

8: IP68


F: Front Fasten (前鎖式/Enclosure Rear Mount)

S: Screw (螺紋式)

S: Solder Type (焊接式)

M: Male Pin (公Pin)

MSAP-03PMMS-SF8001		2.5
MSAP-04PMMS-SF8001		2.5
MSAP-05PMMS-SF8001		2.5
MSAP-06PMMS-SF8001		2.5
MSAP-08PMMS-SF8001		2.5
MSAP-10PMMS-SF8001	4.5	2.5
MSAP-12PMMS-SF8001	4.5	2.5
Item No.	A	B
	Pin伸出長度	



Note:

- * Important Dimension.
- * Waterproof Rate: IP68.
- * Housing: Thermoplastic, Black.
- * Pin: Copper Alloy, Gold Plated.
- * Nut: Thermoplastic, Black.
- * Rated Voltage: 3 & 4Pin 250V dc. or ac.
5Pin 60V dc. or ac.
6~12Pin 30V dc. or ac.
- * Rated Current: 3~5Pin 4A
6~8Pin 2A
10~12Pin 1.5A
- * Operating Temperature: -40~105°C
- * For Panel Thickness Max 4.0mm.
- * Recommended Nut Torque: 4~6 Kgf.cm.

A	UNIT:mm				TITLE N SEN, M12 A -PLASTIC, SCREW RECEPTACLE, M, M, SOLDER			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO MSAP-XXPMMS-SF8001		DRAWN BY Jane		DATE 2020/02/20				
	TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°				SCALE 3:2		SIZE A4			SHEET 1 OF 1		DWG NO MSAP-XXPMMS-SF8001		CHECKED BY Brady		DATE 2020/02/20		
					REV. 01		WC-REV. A.6			CUSTOMER ALTW		APPROVED BY Neo		DATE 2020/02/20				
							QC:Inspection item											
1		2			3			4		5			6		7		8	
																	WI0814-03-00001A	