


SPRING-LOADED PINS

DISCRETE SPRING-LOADED CONTACTS • POWER SPRING PINS

0851

0851-0-15-20-82-14-11-0


Solder Mount in 2,29 min. mounting hole or Surface Mount, 2,21 Ø minimum pad
Also available on 24mm wide carrier tape: 540 parts per 330mm reel
See page 28.5 for Tape & Reel details



0853

0853-0-15-20-82-14-11-0


Solder Mount in 2,29 min. mounting hole or Surface Mount, 2,21 Ø minimum pad size



0854

0854-0-15-20-82-14-11-0


Power spring pin, Soldercup
Accepts wire sizes up to 1,45 Dia.



0855

0855-0-15-20-82-14-11-0


Power spring pin, Wire crimp termination for wire sizes 16 AWG Max. / 20 AWG Min.



0856

0856-0-15-20-82-14-11-0


Power spring pin
Solder Mount in 1,14 min. mounting hole



0859

0859-0-15-20-82-14-11-0


Power spring pin
Surface Mount, 2,54 Ø suggested pad size



0873

0873-0-15-20-82-14-11-0


Solder Mount in 2,29 min. mounting hole or Surface Mount, 2,21 Ø minimum pad size



0850

0850-0-15-20-83-14-11-0


Power spring pin, Solder Mount in 2,29 min. mounting hole
Also available on 32mm wide carrier tape: 500 parts per 330mm reel
See page 28.5 for Tape & Reel details



0858

0858-0-15-20-82-14-11-0


Power spring pin
Solder Mount in .045 min. mounting hole



0878

0878-0-15-20-82-14-11-0

Power spring pin
Solder Mount in .045 min. mounting hole



Material Specifications:

Sleeve & Plunger Material: Copper Alloy

Spring Material: Stainless Steel 302

Sleeve & Plunger Finish: 0,5µm Gold over Nickel

Spring Finish: 0,25µm Gold over Nickel

Dimensions: Millimeters

Tolerances On: Lengths: ± 0,15
Diameters: ± 0,051
Angles: ± 2°

RoHS-2
2011/65/EU

Mechanical & Electrical Specifications:

Durability: Up to 1,000,000 cycles

Rated Current (Free air):

Continuous 9 amps @ 10° C temperature rise

Contact Resistance: 20 mΩ max.

Environmental Specifications:

Operating temperature range:
-55/+125° C (discontinuous)

82, 83 Springs are not interchangeable

Order Code: 08XX - X - XX - 20 - **8X** - 14 - 11 - 0

Spring Number

Spring Number	Mid. Stroke	Max. Stroke	Force @ Mid. Stroke	Initial Force (Pre-Load)
82	1,14	2,29	120 g	25 g
83	1,14	2,29	120 g	25 g



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com