


DIMENSIONS



TIN LEAD PART NUMBER

PART NUMBER


86094647113755121E1

LEAD FREE PART NUMBER

PART NUMBER

86094647113755AGLF

TERMINATION




SPECIFICATION 121 or AGLF = Grounding pins in position : A1 / A32
C1 / C32

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C-8609-0000A

PCB DRILLING

component side



rev	ecn no	dr	date
A	-	-	1997/11/25
B	LS07-0073	HLE	2007/03/07
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection A3	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	ROUILLARD	1997/11/25	ANGULAR	0.X	±0.1	size
Eng	ROUILLARD	1997/11/25	LINEAR	0.XX	±0.1	A3
Chr	P.LEGARE	1997/11/25		0.XXX	±0.1	Scale 1.5
Appr	P.LEGARE	1997/11/25	Product family			ECN
			DIN STD			LS07-0073
			Spec ref			-
FCI			STANDARD MALE 3 ROW			Rev.
			64 CONTACTS			B
catalog no			See table			
			CUSTOMER			sheet 1 of 1