




PRODUCT NUMBER
SEE TABLE, SHT 2



spec ref				dr	BARRY LIANG	2019-05-15	projection 	MM 	size	A3	scale	3:1
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	BARRY LIANG	2019-05-15			ecn no			
ASME Y14.5				chr	-	-			rel level			
-				appr	-	-			In Work			
surface 3.200 linear				Amphenol FCI		title 7.2mm GUIDE MODULE, RIGHT ANGLE 4/5 PAIR			dwg no 10150961			rev 6
ASME Y14.5		0.X ±.3										
		0.XX ±.10										
ASME Y14.5		angular	0° ±2°	cat. no.		Product - Customer Special Drw			sheet 1 of 2			


PRODUCT NUMBER
10150961-101LF



SCALE 2:1

RECOMMENDED PCB LAYOUT NOTE 4

- 1. MATERIAL: ZINC ALLOY
- 2. FINISH: ZINC YELLOW CHROMATE
- 3. APPLICATION SPECIFICATION: GS-20-045
- ④ REFER TO CUSTOMER DRAWING 10035911 FOR INFORMATION REGARDING PBC LAYOUT OF POWER AND GUIDE MODULES RELATIVE TO SIGNAL MODULES
- 5. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 6. PACKAGING MEETS GS-14-920 LEAD FREE LABELING SPECIFICATION.

spec ref				dr	BARRY LIANG	2019-05-15	projection 	MM 	size	A3	scale	2:1			
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	BARRY LIANG	2019-05-15			ecn no						
ASME Y14.5				chr	-	-			rel level						
-				appr	-	-			In Work						
product family							AirMax Accessories								
surface	3.200	linear	0.X	±.3	Amphenol FCi	title				7.2mm GUIDE MODULE, RIGHT ANGLE		dwg no	10150961		rev
ASME Y14.5	angular	0°	±2°	cat. no.											
		0.XX	±.10			4/5 PAIR							6		
		0.XXX	±.050												